



Product: [74040NH](#)

DataTuff Ind SPE 1km10Mb 18AWG SO SF/UTP LSZH

Product Description

DataTuff Ind SPE 1km10Mb 18AWG SO SF/UTP LSZH

Technical Specifications

Product Overview

Suitable Applications:	Long distance sensors in harsh environment at Industrial edge, 1 single pair Ethernet up to 20 MHz
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
18	Solid	BC - Bare Copper	1

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	2.45 mm

Color Chart

Color
White & Blue

Outer Shield Material

Type	Material	Coverage [%]
Tape	Polyester	100%
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	80%

Outer Jacket Material

Material	Nominal Diameter	Min. Wall Thickness	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.60 mm	0.38 mm	0.55 mm

Construction and Dimensions

Min Elongation at Breakof Conductors:	8 %
Min Elongation at Breakof Jacket:	100 MPa
Min Tensile Strength of Jacket:	9 MPa

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]
21.4 Ohm/km at 20°C	2 %

Capacitance

Max. Capacitance Unbalance

1,600 pF/km

Dielectric Strength:	2 kVac/1 min
Insulation Resistance:	5000 MOhm*km

Impedance

Nominal Characteristic Impedance

100 Ohm

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
0.1 MHz	1	15 dB	50 dB	55 dB
1 MHz	1.4	20 dB	40 dB	35 dB
4 MHz	2.6	23 dB	31 dB	23 dB
10 MHz	4.1	25 dB	25 dB	15 dB
20 MHz	5.7	25 dB	20.5 dB	9 dB

Voltage

Non-UL Voltage Rating

300 V

Temperature Range

Operating Temp Range:	-30°C To +80°C
-----------------------	----------------

Mechanical Characteristics

Cold Bend Test:	No Crack
Hygroscopicity:	Weight increasing not exceed 1% (for 3hrs)
Wicking:	The filter paper shall not wet (for 6 hrs)

Standards

UL AWM Style Compliance:	AWM 21307
IEC Compliance:	IEC 61156-13, UL 758

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT2
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	10
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	60

Part Number

Variants

Item #	Color	Putup Type	Length
74040NH-A500	Black	Reel	500 m
74040NH-A1500	Black	Reel	1,500 m

History

Update and Revision:	Revision Number: 0.32 Revision Date: 01-25-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.