



Product: [6640FD](#)

1Pr 24AWG Shielded Data OSDP CMP

Product Description

OSDP Reader Cable, 1 Pair 24 AWG stranded (7x32) tinned copper (data) with foam FEP insulation, Beldfoil® shield w/ drain, with Flamarrest® insulation, Plenum, Flamarrest®

Technical Specifications

Product Overview

Suitable Applications:	OSDP Readers, RS-485, Serial Data, Access Control
------------------------	---

Construction Details

Conductor

Number of Element	Stranding	Material	Notes
2	7x32	TC - Tinned Copper	Twisted Pair Configuration

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.025 in (0.64 mm)	0.074 in (1.9 mm)	White/Blue Stripe & Blue/White Stripe

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Aluminum	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
Flamarrest®	0.015 in (0.38 mm)	0.186 in (4.72 mm)

Overall Cable Diameter (Nominal): 0.186 in (4.72 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedance	Nom. Velocity of Prop.
24 Ohm/1000ft	13 pF/ft (43 pF/m)	120 Ohm	76%

Voltage

UL Voltage Rating
(300 V (CMP))

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.
1.86 in (47.2 mm)

Max. Pull Tension:	28 lbs (13 kg)
Bulk Cable Weight:	16 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	CMP, FT6, NFPA 262
NEC / UL Compliance:	Article 800
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6640FD

History

Update and Revision:	Revision Number: 0.20 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.