



Product: [70001LS](#)

Profibus PA, 1PR #18 Str TC, PO ins, F/B, LSNH Jkt, 300 V

Product Description

Profibus PA, 1 Pair AWG 18 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil + Braid(s) shielding, LSZH / FRNC jacket , 300 V

Technical Specifications

Product Overview

Suitable Applications:	Profibus PA or Foundation FieldBus PA
------------------------	---------------------------------------

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors	No. of Pairs
Pair(s)	18	7x26	TC - Tinned Copper	2	1

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PE - Polyethylene (Foam)	2.5 mm	0.05 mm	0.65 mm

Color Chart

Number	Color
Pair 1	Red & Green

Inner Shield

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)		TC - Tinned Copper	AWG20/7
Braid	Tinned Copper (TC)	85%		

Inner Jacket

Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Black or Blue	8 mm	1.15 mm

Table Notes:	UV Stabilised
--------------	---------------

Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	12.8 mm	0.3 mm	1.27 mm

Construction and Dimensions

Cabling

Description	Filler
1 pair and 2 fillers twisted to cable core	Polyethylene (2x) (1.65 mm)

Armor

Type of Armor	Material	Thickness of Armoring Wires	Coverage Percentage
Steel Wire Armoring	Galvanized steel wire	0.9 mm	Min. 95%

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. Outer Shield DCR
20.5 Ohm/km	9 Ohm/km

Capacitance

Max. Capacitance Conductor to Conductor	Max. Capacitance Unbalance
80 pF/m	4 pF/m

Impedance

Frequency [MHz]	Nominal Characteristic Impedance	Nominal Characteristic Tolerance
0.03125 MHz	100 Ohm	20 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.039 MHz	0.3 dB/100m

Delay

Nominal Velocity of Propagation (VP) [%]
77%

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temperature Range:	-15°C To +70°C
Storage Temperature Range:	-45°C To +70°C
Operating Temp Range (Flexible Install):	-15°C To +70°C
Operating Temp Range (Fixed Install):	-45°C To +70°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-2-1
Max. Pull Tension:	50 N
Min. Bend Radius During Installation:	120 mm
Min Setting Radius:	80 mm

Standards

CENELEC Compliance:	EN 50290-2-20
---------------------	---------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor, Indoor/Outdoor, Outdoor, Indoor/Outdoor - Euroclass Eca
----------------------	---

Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
70001LS.00120	Black	Reel	120 m	8719605009050
70001LS.00500	Black	Reel	500 m	8719605009067
70001LS.001000	Black	Reel	1,000 m	8719605009043
70001LS.01500	Blue	Reel	500 m	8719605009081

70001LS.011000	Blue	Reel	1,000 m	8719605009074
70001LS.021000	Orange	Reel	1,000 m	8719605009098

History

Update and Revision:	Revision Number: 0.222 Revision Date: 04-30-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.