



Product: [7700A](#)

75 Ohm Analog Video Coax, Dual Ultra-miniature RG-59, 30 AWG Str TC, 95% TC French Braids, Flamarrest® Jkt, CMP, Flexible

Product Description

75 Ohm Analog Video Coax, Dual Ultra-miniature RG-59, 30 AWG (7x38) Tinned Copper Conductors, FEP Insulation, 95% Tinned Copper French Braid Inner Shields, Flamarrest® Jacket, CMP, Flexible

Technical Specifications

Product Overview

Suitable Applications:	S-Video, Standard analog video
------------------------	--------------------------------

Construction Details

RG Type:	Ultra-miniature 59
----------	--------------------

Conductor

AWG	Stranding	Nom. Diameter	Material
30	7x38	0.012 in	TC - Tinned Copper

Insulation

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.053 in

Inner Shield Material

Inner Shield Type	Material	Coverage
French Braid	Tinned Copper (TC)	95%

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.215 in

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.7 dB/100ft
5 MHz	1.7 dB/100ft
10 MHz	2.3 dB/100ft
30 MHz	4.1 dB/100ft
50 MHz	5.3 dB/100ft
100 MHz	7.6 dB/100ft
200 MHz	11.8 dB/100ft
400 MHz	17.6 dB/100ft
700 MHz	24.2 dB/100ft
900 MHz	28.0 dB/100ft
1000 MHz	29.8 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
--------------------	-----------------------	---------------------------------	----------------	---------------

92.6 Ohm/1000ft	7.5 Ohm/1000ft	17.3 pF/ft	75 Ohm	78%
-----------------	----------------	------------	--------	-----

Voltage

UL Voltage Rating	Non-UL Voltage Rating
300 V (CMP)	300 V

Mechanical Characteristics

Temperature

UL Rating	Operating
60°C	-10°C to +60°C

Bend Radius

Installation Min.
2.2 in

Bulk Cable Weight:	20 lbs/1000ft
Max. Pull Tension:	12 lbs

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	NFPA 262
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1807A

History

Update and Revision:	Revision Number: 0.307 Revision Date: 09-30-2020
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.