



Product: [7710A](#)



VideoFLEX® Snake, RG6, #18-3 Coax, CMR

Product Description

VideoFLEX® Digital Coax Snake Cable, Riser-CMR, 3-RG6 18 AWG, solid bare copper conductors, foam HDPE core, Duofoil® +95% tinned copper braid, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080p, SDI/HDTV Digital Video, High Definition (HD), Standard Definition (SDI)
------------------------	------------------------------------------------------------------------------------------------------------------------------------

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BC - Bare Copper	0.04 in	3
Conductor Count:				3

Insulation	
Material	Nominal Diameter
PE - Polyethylene (Foam)	0.18 in
Table Notes:	Gas Injected

Color Chart	
Number	Color
1	Red
2	Green
3	Blue

Inner Shield				
Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		95%

Inner Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.275 in

Outer Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.746 in

Electrical Characteristics

Conductor DCR				
Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
6.4 Ohm/1000ft	6.4 Ohm/1000ft		3 Ohm/1000ft	3.0 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
5-1600 MHz	23 dB
1600-4500 MHz	21 dB
4500-6000 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.24 dB/100ft
3.58 MHz	0.44 dB/100ft
5 MHz	0.52 dB/100ft
7 MHz	0.61 dB/100ft
10 MHz	0.71 dB/100ft
67.5 MHz	1.65 dB/100ft
71.5 MHz	1.69 dB/100ft
88.5 MHz	1.86 dB/100ft
100 MHz	1.95 dB/100ft
135 MHz	2.24 dB/100ft
143 MHz	2.3 dB/100ft
180 MHz	2.57 dB/100ft
270 MHz	3.17 dB/100ft
360 MHz	3.69 dB/100ft
540 MHz	4.6 dB/100ft
720 MHz	5.38 dB/100ft
750 MHz	5.5 dB/100ft
1000 MHz	6.42 dB/100ft
1500 MHz	7.99 dB/100ft
2000 MHz	9.37 dB/100ft
2250 MHz	10.01 dB/100ft
3000 MHz	11.78 dB/100ft
4500 MHz	14.7 dB/100ft
6000 MHz	17.7 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.24 ns/ft	82%

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	60°C
Operating Temperature Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	243 lbs/1000ft
Max. Pull Tension:	207 lbs
Min. Bend Radius/Minor Axis:	8 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	AWM 1354 (each coax), AWM 2688 (overall)

CPR Euroclass:	Eca
RG Type:	6
Series Type:	6

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
7710A B59500	Black, Matte	Reel	500 ft	612825357315
7710A B591000	Black, Matte	Reel	1,000 ft	612825357292

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.401 Revision Date: 04-29-2024
----------------------	--------------------------------------------------

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.