



Product: [70075](#)

1 PAIR AES/EBU, 24AWG, ISTP, FRNC/LSZH

Product Description

1 PAIR AES/EBU, 24AWG, ISTP, FRNC/LSZH

Technical Specifications

Product Overview

Suitable Applications:	Digital multi-modulation cable used in professional studios; For the transmission of analogue and digital audio signals; Designed to meet the requirements of the AES/EBU specification
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Cross Section	Construction n x D
24	7x32	BC-OFHC - Oxygen-Free Bare Copper (High Conductivity)	0.22 mm ²	7x0.20 mm

Conductor Count:	2
Total Number of Pairs:	1

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	PE - Polyethylene (Foam)	1.45 mm	0.03 mm

Color Chart

Number	Color
Pair 1	Black & Red

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	24	7x0.20 mm

Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	3.50 mm	0.10 mm

Construction and Dimensions

Cabling

Description
1 pair

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
86.0 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor

40 pF/m

Impedance

Frequency [MHz]	Nominal Characteristic Impedance	Nominal Characteristic Tolerance
0.1 - 6	110 Ohm	+/- 15 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
80%

Temperature Range

Other Temp Range:	-30 to +70 °C
-------------------	---------------

Mechanical Characteristics

Min. Bend Radius During Installation:	35 mm
Min. Bend Radius During Operation:	52.5 mm

Standards

CPR Euroclass:	Dca-s2,d1,a1
----------------	--------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
----------------------	------------------------

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
70075.01305	Black	Reel	305 m	8719605010681
70075.01500	Black	Reel	500 m	8719605010698

History

Update and Revision:	Revision Number: 0.182 Revision Date: 02-15-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.