



Product: [70077](#)

1 PAIR AES/EBU, 24AWG, ISTP, spiral serve PVC

## Product Description

DIGITAL AUDIO 1 PAIR AES/EBU, 24AWG/0.22mm<sup>2</sup>, ISTP, bare copper spiral serve, PVC

## Technical Specifications

### Product Overview

Suitable Applications:	Digital multi-modulation cable used in professional studios for the transmission of analogue and digital audio signals.; Designed to meet the requirements of the AES/EBU specification; The cable is very flexible and has a small outer diameter for use in applications where space is limited
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	BC - Bare Copper	1

Conductor Count:	2
Total Number of Pairs:	1

#### Insulation

Material	Nominal Diameter
PE - Polyethylene	1.55 mm

#### Color Chart

Number	Color
Pair 1	White & Blue

#### Outer Shield

Type	Material	Coverage [%]
Spiral Serve / Screen	Bare Copper (BC)	90%

#### Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance
PVC - Polyvinyl Chloride	6.5 mm	0.2 mm

Table Notes:	Flexible Matte Finish Sheath
--------------	------------------------------

### Construction and Dimensions

#### Cabling

Description
1 Pair + 2 fillers

### Electrical Characteristics

#### Conductor DCR

Max. Conductor DCR
87 Ohm/km

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
60 pF/m	45 pF/m

#### Inductance

Nominal Inductance
0.75 $\mu$ H/m

#### Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance
110 Ohm	11 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.15 MHz	0.3 dB/100m
1 MHz	1.5 dB/100m
4 MHz	3.8 dB/100m
10 MHz	6 dB/100m
20 MHz	8.5 dB/100m

#### Temperature Range

Installation Temperature Range:	-5°C To +50°C
Operating Temperature Range:	-30°C To +70°C
Other Temp Range:	-30-+70 °C

#### Mechanical Characteristics

Min Setting Radius:	26 mm
---------------------	-------

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

#### Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
LOI of Jacket:	34 %
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	10 $\mu$ S/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

#### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	EAN
70077.00500	Gray	Reel	500 m	8719605010704

#### History

Update and Revision:	Revision Number: 0.191 Revision Date: 10-21-2024
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.