



Product: [7732A](#)

75 Ohm SDI Coax, RG-11, 14 AWG Solid BC, Foil + 95% TC Braid, PVDF Jkt, CMP

Product Description

75 Ohm SDI Coax, RG-11, 14 AWG Solid Bare Copper Conductor, FEP Insulation, Foil + 95% Tinned Copper Braid Shield, PVDF Jacket, CMP

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | Digital Video, 6 Gb/s UHDTV, HD-SDI 1080p |
|------------------------|---|

Construction Details

| | |
|----------|----|
| RG Type: | 11 |
|----------|----|

Conductor

| AWG | Stranding | Nom. Diameter | Material |
|-----|-----------|---------------|------------------|
| 14 | Solid | 0.064 in | BC - Bare Copper |

Insulation

| Material | Nom. Diameter |
|---|---------------|
| FEP - Fluorinated Ethylene Propylene (Foam) | 0.274 in |

Outer Shield Material

| Layer | Outer Shield Type | Material | Material Trade Name | Coverage |
|-------|-------------------|-------------------------------|---------------------|----------|
| 1 | Tape | Tri-Laminate (Alum+Poly+Alum) | Duofoil® | 100% |
| 2 | Braid | Tinned Copper (TC) | | 95% |

Outer Jacket Material

| Material | Nom. Diameter |
|--------------------------------|---------------|
| PVDF - Polyvinylidene Fluoride | 0.348 in |

Electrical Characteristics

Return Loss (RL)

| Frequency [MHz] | Min. Return Loss [dB] |
|-----------------|-----------------------|
| 5 - 1600 MHz | 23 dB |
| 1600 - 4500 MHz | 21 dB |
| 4500 - 6000 MHz | 15 dB |

Attenuation

| Frequency | Nom. Attenuation [dB/100ft] |
|-----------|-----------------------------|
| 1 MHz | 0.15 dB/100ft |
| 3.58 MHz | 0.26 dB/100ft |
| 5 MHz | 0.3 dB/100ft |
| 7 MHz | 0.34 dB/100ft |
| 10 MHz | 0.4 dB/100ft |
| 67.5 MHz | 1.2 dB/100ft |
| 71.5 MHz | 1.24 dB/100ft |
| 88.5 MHz | 1.4 dB/100ft |

| | |
|----------|----------------|
| 100 MHz | 1.5 dB/100ft |
| 135 MHz | 1.55 dB/100ft |
| 143 MHz | 1.65 dB/100ft |
| 180 MHz | 1.83 dB/100ft |
| 270 MHz | 2.31 dB/100ft |
| 360 MHz | 2.76 dB/100ft |
| 540 MHz | 3.57 dB/100ft |
| 720 MHz | 4.32 dB/100ft |
| 750 MHz | 4.44 dB/100ft |
| 1000 MHz | 5.42 dB/100ft |
| 1500 MHz | 7.06 dB/100ft |
| 2000 MHz | 8.57 dB/100ft |
| 2500 MHz | 9.93 dB/100ft |
| 3000 MHz | 11.27 dB/100ft |
| 4500 MHz | 14.67 dB/100ft |
| 6000 MHz | 17.86 dB/100ft |

Electricals

| Nom. Conductor DCR | Nom. Outer Shield DCR | Nom. Capacitance Cond-to-Shield | Nom. Impedence | Nom. Velocity |
|--------------------|-----------------------|---------------------------------|----------------|---------------|
| 2.5 Ohm/1000ft | 1.6 Ohm/1000ft | 16.3 pF/ft | 75 Ohm | 83% |

Voltage

| UL Voltage Rating |
|-------------------|
| 300 V (CMP) |

Mechanical Characteristics

Temperature

| UL Rating | Operating |
|-----------|-----------------|
| 125°C | -20°C to +125°C |

Bend Radius

| Installation Min. |
|-------------------|
| 3.5 in |

| | |
|--------------------|---------------|
| Bulk Cable Weight: | 83 lbs/1000ft |
| Max. Pull Tension: | 145 lbs |

Standards and Compliance

| | |
|---------------------------------|---|
| Environmental Suitability: | Indoor/Outdoor, Indoor, Outdoor, UV Resistance |
| Sustainability: | CA Prop 65 |
| Flammability / Fire Resistance: | NFPA 262, FT6 |
| NEC / UL Compliance: | CMP |
| CEC / C(UL) Compliance: | CMP |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |
| Non-Plenum Number: | 7731A |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.359 Revision Date: 02-16-2021 |
|----------------------|--|

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.