



Product: [7784AS](#) 

7784AS - Triax 11, 15 AWG Solid SPC, Double BC Braids, PVC Jkt



Product Description

Triax 11, 15 AWG Solid Silver plated Copper Conductor, PE Insulation, 80% Silver plated Copper Braid Shield, PE Insulation, 80% Bare Copper Braid Shield, PVC Jacket.

Technical Specifications

Product Overview

Suitable Applications:	Analog Video; Interconnect camera to CCU (camera control unit)
------------------------	--

Construction Details

Series Type:	Triax 8/11/14
--------------	---------------

Conductor

Number of Element	Size	Stranding	Nom. Diameter	Material
1	15 AWG	Solid	1.4 in	SC - Silvered Copper

Insulation

Element	Material	Nom. Insulation Diameter
Insulated Conductor	PE - Polyethylene (Foam)	6.5 mm (0.26 in)

Inner Shield

Shield Type	Material	Coverage
Braid	Silvered Copper (SC)	80%

Inner Jacket

Material	Nom. Diameter
PE - Polyethylene	8.5 mm (0.33 in)

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	80%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	11.2 mm

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
5 MHz	1.2 dB/100m
50 MHz	3.6 dB/100m
71.5 MHz	4.3 dB/100m
88.5 MHz	4.8 dB/100m
100 MHz	5.2 dB/100m
180 MHz	7.1 dB/100m
270 MHz	8.8 dB/100m

750 MHz	15.2 dB/100m
1000 MHz	18 dB/100m
1500 MHz	22 dB/100m
2000 MHz	26 dB/100m
2500 MHz	32 dB/100m
3000 MHz	34 dB/100m

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
11 Ohm/km	9 Ohm/km (2.7 Ohm/1000ft)	7 Ohm/km (2.1 Ohm/1000ft)	55 pF/m (17 pF/ft)	75 Ohm	81%

Screening

Frequency	Min. Screening Attenuation
30 - 850 MHz	75 dB

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +70°C	-5°C To +70°C	-40°C To +70°C

Bend Radius

Stationary Min.
110 mm (4.3 in)

Max. Pull Tension:	300 N (67 lbf)
--------------------	----------------

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor - Euroclass Eca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
CENELEC Compliance:	EN 50117-1
European Directive Compliance:	EU CE Mark
Other Standard Compliance(s):	HD-SDI, dual link HD-SDI and 3G-SDI

History

Update and Revision:	Revision Number: 0.216 Revision Date: 04-08-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
7784AS.02500	Red	Reel	500 m	8719605014375
7784AS.021000	Red	Reel	1,000 m	8719605014351
7784AS.K21000	Red	Reel	1,000 m	8719605173010
7784AS.021525	Red	Reel	1,525 m	8719605014368

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.