



Part Number: 7805

RF 100 Wireless Coax, RG174, #25

Product Description

RG-174 type, 25 AWG solid .018" bare copper conductor, solid polyethylene insulation, Beldfoil®; tinned copper braid shield (90% coverage), PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	Solid	BC - Bare Copper	0.018 in	1

Conductor Count:	1
Conductor Size:	25 AWG

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.061 in

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum/Polyester	Beldfoil®	100 %
Braid	2	TC - Tinned Copper		90 %

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.11 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
32 Ohm/1000ft	32 Ohm/1000ft		9.1 Ohm/1000ft	9.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
31.2 pF/ft

Shielding:	Foil + Braid(s)
------------	-----------------

Inductance

Nominal Inductance
0.077 μ H/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss

5 MHz	1.5 dB/100ft
10 MHz	2.2 dB/100ft
30 MHz	3.8 dB/100ft
50 MHz	4.9 dB/100ft
150 MHz	8.6 dB/100ft
220 MHz	10.4 dB/100ft
450 MHz	15.2 dB/100ft
900 MHz	22 dB/100ft
1500 MHz	28.7 dB/100ft
1800 MHz	31.7 dB/100ft
2000 MHz	33.4 dB/100ft
2500 MHz	37.8 dB/100ft
3000 MHz	42 dB/100ft
3500 MHz	45.4 dB/100ft
4500 MHz	52.3 dB/100ft
5800 MHz	60.9 dB/100ft
6000 MHz	62 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
30 MHz	216 W	216 W
50 MHz	154 W	154 W
150 MHz	74 W	74 W
220 MHz	48 W	57 W
450 MHz	34 W	34 W
900 MHz	21 W	21 W
1,500 MHz	14 W	14 W
2,000 MHz	12 W	13 W
2,500 MHz	10 W	12 W
3,500 MHz	8 W	10 W
4,500 MHz	7 W	9 W
6,000 MHz	5 W	8 W
4,500 MHz		7 W
5,800 MHz		5 W
6,000 MHz		5 W

Voltage

Non-UL Voltage Rating
1100 V RMS

VSWR

Frequency [MHz]	Max. VSWR
5-6000 MHz	1.25:1

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	9 lbs/1000ft
Max Recommended Pulling Tension:	16 lbs
Min Bend Radius/Minor Axis:	1.25 in

Standards

RG Type:	174/U Type
RG / Series Type:	174/U Type

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
7805 010100	Black	E
7805 0101000	Black	
7805 010500	Black	

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.
-----------	--

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.