



Product: [7817A](#)

SMPTE 311M Double Jacket, 2 Fiber, 2 Conductor 24 AWG, 4 Conductor 20 AWG

Product Description

12mm Double Jacketed SMPTE 311M Studio Cable, 4 power conductors, SM fibers w/24 and 20 AWG stranded (7x32 and 19x32) TC conductors, PE insulation, TC braid shield (85% coverage), Belflex® jacket.

Technical Specifications

Product Overview

Suitable Applications:	SMPTE 311M Camera Cable
------------------------	-------------------------

Multiconductor

Multiconductor Conductor and Insulation

Element	No. of Conductors	AWG	Stranding	Material	Nominal Conductor DCR	Insulation Material	Insulation Nominal Diameter
24 AWG	2	24	7x32	TC - Tinned Copper	23.3 Ohm/1000ft	PE - Polyethylene	0.048 in
20 AWG	4	20	19x32	TC - Tinned Copper	8.8 Ohm/1000ft	PE - Polyethylene	0.062 in

Multiconductor Color Chart

Description	Color
24 AWG	Red
24 AWG	Gray
20 AWG	White
20 AWG	Black

Shielding:	Braid
------------	-------

Multiconductor Inner Jacket

Element	Material	Nominal Diameter
Overall	PVC - Polyvinyl Chloride	0.357 in

Multiconductor UL Voltage

UL Description	UL Voltage Rating
24 AWG	300 V RMS
20 AWG	300 V RMS

Fiber

Fiber Cable Construction

Fiber Type	Fiber Count
OS2, G.657.A2	2

Fiber Color Coding:	Yellow, Blue
---------------------	--------------

Buffer Specification

Buffer Material	Buffer Diameter
PVC - Polyvinyl Chloride	900 µm

Mode Field Diameter:	9.2 µm
Wavelength@Optical SM1:	1310 nm, 1550 nm
Max. Attenuation at 1310 nm:	0.50 dB/km

Max. Attenuation at 1550 nm:	0.50 dB/km
------------------------------	------------

Overall Cable

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
PVC - Polyvinyl Chloride	0.472 in	0.058 in	PVC - Polyvinyl Chloride

Overall Shielding

Layer 1	Type	Material	Coverage
Overall	Braid	TC - Tinned Copper	85 %

Jacket:	PVC
Separator Material@OuterJacket1 1:	PVC - Polyvinyl Chloride
Operating Temperature Range:	-40°C to 70°C
Installation Temperature Range:	-10°C to 70°C
Storage Temperature Range:	-40°C to 70°C
Max. Pull Tension:	1350 N
Bulk Cable Weight:	108 lbs/1000ft

Applicable Standards & Environmental Programs

EU Directive Compliance:	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
CA Prop 65 (CJ for Wire and Cable):	Yes
China RoHS II (GB/T 26572-2011):	Yes

Suitability

Suitability - Outdoor:	Yes
------------------------	-----

Flame Test

UL Flammability:	VW-1
------------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Product Notes

Notes:	Bend Radius is based upon (FOTP-37) @ 20°C. Plenum version and other conductor counts/diameters available by special order.
--------	---

History

Update and Revision:	Revision Number: 0.151 Revision Date: 11-27-2023
----------------------	--

Variants

Item #	Color	UPC	Length
7817A 0101000	Black	612825189909	1,000 ft

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.