



**Product:** [74009](#) 

XGIE, 4PR , Sol, Polyolefin, 300 V RMS, CMR 75C, PLTC 75C, CMX 75C, OIL RES I, CSA C(UL) TYPE CMR, CSA FT4

## Product Description

XGIE, 4 Pair 22 AWG (SOLID) BC - Bare Copper, Polyolefin Insulation, Black PVC Outer Jacket, CMR 75C, PLTC 75C, CMX 75C, OIL RES I, CSA C(UL) TYPE CMR, CSA FT4 C(UL) TYPE CMR, FT4 UL FT4; CSA FT4

## Technical Specifications

### Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/patents">https://www.belden.com/patents</a> .

### Construction Details

#### Conductor

Element	Size	Stranding	Material	No. of Pairs
Pair(s)	22 AWG	Solid	BC - Bare Copper	4

#### Insulation

Element	Material	Nom. Insulation Diameter	Color Code
Pair(s)	PO - Polyolefin	0.048 in (1.2 mm)	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

#### Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.301 in (7.65 mm)	Yes

Overall Cable Diameter (Nominal):	0.301 in (7.65 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Max. Conductor DCR	Max. Capacitance Unbalance	Nom. Characteristic Impedance
Pair(s)	56.5 Ohm/km (17.2 Ohm/1000ft)	66 pF/100m	100 Ohm

#### Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
510 ns/100m	25 ns/100m	70%

#### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	65.3	65.3	63.3	63.3	63.8	60.8	20	100 ± 12	105 ± 10
4	4.0 dB/100m	56.3	56.3	52.3	52.3	51.7	48.7	23	100 ± 12	100 ± 10
8	5.7 dB/100m	51.8	51.8	46.1	46.1	45.7	42.7	24.5	100 ± 12	100 ± 10
10	6.4 dB/100m	50.3	50.3	43.9	43.9	43.8	40.8	25	100 ± 12	100 ± 10
16	8.1 dB/100m	47.3	47.3	39.1	39.1	39.7	36.7	25	100 ± 12	100 ± 10
20	9.2 dB/100m	45.8	45.8	35.2	35.2	37.7	34.7	25	100 ± 12	100 ± 10
25	10.3 dB/100m	44.3	44.3	34.1	34.1	35.8	32.8	24.3	100 ± 15	100 ± 10

31.25	11.6 dB/100m	42.9	42.9	31.3	31.3	33.9	30.9	23.6	100 ± 15	100 ± 10
62.5	16.8 dB/100m	38.4	38.4	21.6	21.6	27.8	24.8	21.5	100 ± 15	100 ± 10
100	21.7 dB/100m	35.3	35.3	17.1	17.1	23.8	20.8	20.1	100 ± 15	
155	27.7 dB/100m	32.5	32.5	4.7	4.7	19.9	16.9	19	100 ± 18	
200	32 dB/100m	30.8	30.8	3	3	17.7	14.7	19	100 ± 20	
250	36.4 dB/100m	29.3	29.3	0	0	15.8	12.8	18	100 ± 20	
300	40.5 dB/100m	28.2	28.2	0	0	14.2	11.2	18	100 ± 20	
310	41.3 dB/100m	27.9	27.9			13.9	10.9	18	100 ± 20	
350	44.3 dB/100m	27.2	27.2			12.9	9.9	17	100 ± 22	

#### Voltage

UL Voltage Rating
(PLTC, CMR/CMX-Outdoor), 600 V (AWM)

#### Mechanical Characteristics

#### Temperature

UL Temperature	Operating	Installation	Storage
60°C	-25°C To +75°C	-10°C To +75°C	-25°C To +75°C

#### Bend Radius

Stationary Min.
1.2 in (30 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	42 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, Article 725, CMR, CMX-Outdoor, PLTC
AWM Compliance:	AWM 21047
CEC / C(UL) Compliance:	CMR
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

#### Product Notes

Notes:	ALPHA WIRE-NM P/N 74009 4PR 22 AWG VERIFIED (UL) CAT 5E PLTC OR CMR-CMX OUTDOOR OR C(UL) CMR --- ISO/IEC 11801 CAT 5E SUN RES OIL RES --- US PATENT 6273977 CE ROHS (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FT
--------	--

#### History

Update and Revision:	Revision Number: 0.6 Revision Date: 07-08-2026
----------------------	--

#### Part Numbers

#### Variants

Item #	Color	Putup Type	Length
74009 BK002	Black	Reel	500 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.