



Product: [74011PU](#)

DataTuff® 6A, 4PR #23 Str BC, PO ins, S/FTP, PUR HF jkt, PROFINET Type B, AWM 21292

Product Description

DataTuff® 6A, 4 Pair AWG 23 Bare Copper - Stranded, Polyethylene insulation, S/FTP - Overall Braid / Individual Foil shielding, PUR Halogen Free jacket , PROFINET Type B, AWM 21292

Technical Specifications

Product Overview

Suitable Applications:	PROFINET Cat6A, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
------------------------	--

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Pairs	No. of Elements
Individual Shielded Pair	23 AWG	Stranded	BC - Bare Copper	4	8

Insulation

Element	Material	Nom. Insulation Diameter	Color Code
Individual Shielded Pair	PE - Polyethylene (Foam)	1.58 mm (0.0622 in)	White & Blue, White & Orange, White & Green, White & Brown

Cable Core

Description
4 pairs twisted to cable core

Inner Shield

Element	Shield Type	Material	Coverage
Individual Shielded Pair	Tape	Bi-Laminate (Alum+Poly)	100%

Table Notes:	Aluminum outside
--------------	------------------

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	85%

Outer Jacket

Material	Nom. Diameter
PUR - Polyurethane	8.7 mm (0.34 in)

Overall Cable Diameter (Nominal):	8.7 mm (0.34 in)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
71.9 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
25 ns/100m	78%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. ELTCTL [dB]
1	2.1	75.3	73.2	70.2	68	20	35
4	3.8	66.3	62.5	59.5	56	23	23
10	5.9	60.3	54.4	51.4	48	25	15
16	7.5	57.2	49.8	46.8	43.9	25	10.9
31.2	10.5	52.9	42.4	39.4	38.1	23.6	5.1
62.5	15.0	48.4	33.4	30.4	32.1	21.5	
100	19.1	45.3	26.6	23.2	28.0	20.1	
125	21.5	43.8	22.3	19.3	26.1	19.4	
200	27.6	40.8	13.2	10.2	22.0	18	
250	31.1	39.3	8.3	5.3	20.0	17.3	
300	34.3	38.1	3.9	0.9	18.5	17.3	
500	45.3	34.8			14.0	17.3	

Table Notes:	Limits below 4MHz are for information only
Transfer Impedance Class:	Grade 1
Screening Class:	Type I
Table Notes:	Coupling Attenuation

Voltage

Voltage Rating
30 V AC

Mechanical Characteristics

Temperature

Operating	Storage
-40°C to +80°C	-40°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
45 mm (1.8 in)	90 mm

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Fca, Indoor, Sunlight Resistance - Black only, Oil Resistance
Flammability / Reaction to Fire:	Horizontal, IEC 60332-1-2, UL Horizontal flame
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
Data Category:	Category 6A
ISO/IEC Compliance:	ISO/IEC 11801-1
CENELEC Compliance:	EN 50173-1, Segregation class according EN50174-2 = d
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = Zero
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.275 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
74011PU.00100	Green	Reel	100 m	8719605130235
74011PU.00500	Green	Reel	500 m	8719605128621

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.