



Product: [74045NH](#)

DataTuff Ind SPE 400m10Mb 22AWG SO U/UTP LSZH

Product Description

DataTuff Ind SPE 400m10Mb 22AWG SO U/UTP LSZH Cable

Technical Specifications

Product Overview

Suitable Applications:	Long distance sensors in harsh environment at Industrial edge, 1 single pair Ethernet up to 20 MHz. IEEE 802.3cg(10Base-T1L)
------------------------	--

Construction Details

Conductor

Size	Material
22 AWG	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	1.24 mm (0.0488 in)	White, Blue

Outer Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

Overall Cable Diameter (Nominal):	3.70 mm (0.146 in)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR
59.1 Ω /km

Table Notes:	Min. resistance unbalance within a pair is 2%
--------------	---

High Frequency

Frequency	Max. Insertion Loss (Attenuation)	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Nom. Characteristic Impedance [Ohm]
0.1	1.37 dB	15	50	
1 MHz	2.08 dB	15	50	
4 MHz	3.81 dB	23	50	
10 MHz	5.93 dB	25	50	
20 MHz	8.38	25	50	100

Table Notes:	Characteristic Impedance at 20 MHz with tolerance of ± 15
--------------	---

Voltage

UL Voltage Rating	Breakdown Voltage
300 V	2KVac/min

Mechanical Characteristics

Temperature

Operating
-40 to + 80

Bulk Cable Weight:	17.57 kg/km (11.81 lbs/1000ft)
--------------------	--------------------------------

Standards and Compliance

AWM Compliance:	AWM 21307
Data Category:	SPE 10 Mbps
ISO/IEC Compliance:	IEC 61156-13, UL 758, IEC 61034-2 - Smoke Density Min Transmittance = 70%
European Halogen Free Standards:	IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 , IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.23 Revision Date: 07-08-2024
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
74045NH-A500	Black	Reel	500 m	8719605218216

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.