



Product: [7844R](#)

4-Channel SMPTE Stadium Cable, 8 Fiber, 8 Conductor 18 AWG, 8 Conductor 24 AWG, CMR

Product Description

4-Channel SMPTE Stadium Cable, 8 Single Mode Fiber, 8 TC Conductor (19x30) 18 AWG and 8 TC Conductor (7x32) 24 AWG, PVC Insulation, Beldfoil Shield, PVC Jacket, Riser

Technical Specifications

Product Overview

Suitable Applications:	4 Channel Composite Camera Cable
------------------------	----------------------------------

Multiconductor

Multiconductor Conductor and Insulation

Element	No. of Conductors	AWG	Stranding	Material	Nominal Conductor DCR	Insulation Material	Insulation Nominal Diameter
Quad 1, Quad 2, Quad 3, Quad 4	8	24	7x32	TC - Tinned Copper	23.3 Ohm/1000ft Ohm/1000ft	PVC - Polyvinyl Chloride	0.038 in
Quad 1, Quad 2, Quad 3, Quad 4	8	18	19x30	TC - Tinned Copper	6.67 Ohm/1000ft	PVC - Polyvinyl Chloride	0.080 in

Multiconductor Color Chart

Description	Color
Quad 1 - 24 AWG	Red
Quad 1 - 24 AWG	Gray
Quad 1 - 18 AWG	White
Quad 1 - 18 AWG	Black
Quad 2 - 24 AWG	Red/Yellow
Quad 2 - 24 AWG	Gray/Yellow
Quad 2 - 18 AWG	White/Yellow
Quad 2 - 18 AWG	Black/Yellow
Quad 3 - 24 AWG	Red/Orange
Quad 3 - 24 AWG	Gray/Orange
Quad 3 - 18 AWG	White/Orange
Quad 3 - 18 AWG	Black/Orange
Quad 4 - 24 AWG	Red/Blue
Quad 4 - 24 AWG	Gray/Blue
Quad 4 - 18 AWG	White/Blue
Quad 4 - 18 AWG	Black/Blue

Shielding:	Multiple or Specialty
------------	-----------------------

Multiconductor Inner Shield

Layer	Inner Shield Type	Inner Shield Material	Inner Shield Coverage	Drainwire AWG	Drainwire Stranding	Drainwire Material	Drainwire Diameter	Drainwire Position
Each Quad	Tape	Al/poly (Foil in)	100.0 %	22	7x30	TC - Tinned Copper	0.030 in	Under Each Quad's Shield Tape

Multiconductor UL Voltage

UL Description	UL Voltage Rating
24 AWG	300 V RMS
18 AWG	300 V RMS

Fiber

Fiber Cable Construction

Fiber Type	Fiber Count
OS2, G.657.A2	8

Fiber Color Coding:	Yellow Printed
Subunit Diameter:	0.078 in (2.0 mm)

Buffer Specification

Buffer Material	Buffer Diameter
PVC - Polyvinyl Chloride	900 µm

Number of Active Subunits:	8
Number of Subunit Positions:	8
Fibers Per Subunit:	1
Mode Field Diameter:	9.2 µm
Wavelength@Optical SM1:	1310 nm, 1550 nm
Max. Attenuation at 1310 nm:	0.50 dB/km
Max. Attenuation at 1550 nm:	0.50 dB/km

Overall Cable

Outer Jacket

Nominal Diameter
0.510 in

Jacket:	PVC
Operating Temperature Range:	-20°C to 60°C
Max. Pull Tension:	170 lbs
Bulk Cable Weight:	187 lbs/1000ft

Applicable Standards & Environmental Programs

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
Other Standards:	SMPTE 311
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
CA Prop 65 (CJ for Wire and Cable):	Yes
China RoHS II (GB/T 26572-2011):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flame Test

CSA/C(UL) Flammability:	FT4, UL 1666 Vertical Shaft
-------------------------	-----------------------------

Plenum/Non-Plenum

Plenum (Y/N):	N
---------------	---

History

Update and Revision:	Revision Number: 0.22 Revision Date: 09-20-2023
----------------------	-------------------------------------------------

Variants

Item #	Color	Length
7844R 0101000	Black	1,000 ft
7844R 0104000	Black	4,000 ft

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.