



**Part Number: 7883A**

**CAT6 Patch, 4pr, UTP, PVC Jkt, CMR**

**Product Description**

CAT6 (250MHz), 4-Pair, U/UTP-unshielded, Riser-CMR, Premise Patch cable, 24 AWG solid bare copper conductors, polyolefin insulation, central filler, PVC jacket, RG-45 compatible

**Technical Specifications**

**Product Overview**

Environmental Space:	Riser
Suitable Applications:	Premise Patch Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

**Insulation**

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

**Color Chart**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

**Outer Jacket Material**

Material	Nominal Diameter	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.205 in	No	Central Filler

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	5 %

**Capacitance**

Max. Capacitance Unbalance	Nom. Mutual Capacitance
160 pF/100m	15 pF/ft

**Delay**

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	70 %

## High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.4 dB/100m	74.3 dB	72.3 dB	67.8 dB	64.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	4.5 dB/100m	65.3 dB	63.3 dB	55.8 dB	52.7 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	6.4 dB/100m	60.8 dB	58.8 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	7.1 dB/100m	59.3 dB	57.3 dB	47.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	9.1 dB/100m	56.2 dB	54.3 dB	43.7 dB	40.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	10.2 dB/100m	54.8 dB	52.8 dB	41.8 dB	38.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	11.4 dB/100m	53.3 dB	51.3 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	12.8 dB/100m	51.9 dB	49.9 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm	35.1 dB	5.1 dB
62.5 MHz	18.5 dB/100m	47.4 dB	45.4 dB	31.9 dB	28.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	32.0 dB	
100 MHz	23.8 dB/100m	44.3 dB	42.3 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm	30.0 dB	
155 MHz	30.2 dB/100m	41.5 dB	39.5 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 22 Ohm	100 ± 15 Ohm	28.1 dB	
200 MHz	34.8 dB/100m	39.8 dB	37.8 dB	21.8 dB	18.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 15 Ohm	27.0 dB	
250 MHz	39.4 dB/100m	38.3 dB	36.3 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 15 Ohm	26.0 dB	

Segregation class according EN50174-2:

a

## Voltage

### UL Voltage Rating

300 V RMS

## Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	20 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius During Installation:	2.25 in
Min Bend Radius/Minor Axis:	1.0 in

## Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E Patch
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6 Patch, ANSI/NEMA WC-66 Category 6 Patch
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6 Patch
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6 Patch

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	UPC	Length	Footnote
7883A 0101000	Black	612825190660	1,000 ft	C
7883A 0101000	Black	612825190660	1,000 ft	C
7883A 0061000	Blue	612825190639	1,000 ft	C
7883A 0061000	Blue	612825190639	1,000 ft	C
7883A F2V1000	Gray	612825190585	1,000 ft	C
7883A F2V1000	Gray	612825190585	1,000 ft	C
7883A 0051000	Green	612825190622	1,000 ft	C
7883A 0051000	Green	612825190622	1,000 ft	C
7883A 0031000	Orange	612825190608	1,000 ft	C
7883A 0031000	Orange	612825190608	1,000 ft	C
7883A 0071000	Purple	612825190646	1,000 ft	C
7883A 0071000	Purple	612825190646	1,000 ft	C
7883A 0021000	Red	612825190592	1,000 ft	C
7883A 0021000	Red	612825190592	1,000 ft	C
7883A 0091000	White	612825190653	1,000 ft	C
7883A 0091000	White	612825190653	1,000 ft	C
7883A 0041000	Yellow	612825190615	1,000 ft	C
7883A 0041000	Yellow	612825190615	1,000 ft	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	<a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a>

## Product Notes

Notes:	Print Includes Descending Footage Markings.
--------	---

## History

Update and Revision:	Revision Number: 0.329 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.