



**Product:** [7501A](#)

MachFlex™, Vision Coax 75Ω, #25 Str BC, PO Ins, OA TC Brd, PVC Jkt, AWM 1354

[Request Sample](#)

**Product Description**

MachFlex™ for High Flex, 1 Conductor 25AWG (19x38) Bare Copper, PO Insulation, Overall Tinned Copper Braid(95%) Shield, PVC Outer Jacket, AWM 1354

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	19x38	BC - Bare Copper	0.019 in	1

Conductor Count: 1

**Insulation**

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.09 in

**Outer Shield**

Type	Material	Coverage [%]
French Braid	Tinned Copper (TC)	95%

**Outer Jacket**

Material	Material Trade Name	Nominal Diameter
PVC - Polyvinyl Chloride	Belflex®	0.146 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
35 Ohm/1000ft	9.1 Ohm/1000ft	9.1 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
17.7 pF/ft

**Inductance**

Nominal Inductance
0.097 μH/ft

**Impedance**

Nominal Characteristic Impedance
75 Ohm

**High Frequency (Nominal/Typical)**

Frequency [MHz]	Nom. Insertion Loss
2.2 MHz	0.6 dB/100ft
5 MHz	0.9 dB/100ft
10 MHz	1.3 dB/100ft

30 MHz	2.2 dB/100ft
50 MHz	2.9 dB/100ft
100 MHz	4.2 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.3 ns/ft	77%

#### High Frequency

Frequency [MHz]
2.2 MHz
5 MHz
10 MHz
30 MHz
50 MHz
100 MHz

#### Voltage

UL Voltage Rating
30 V RMS

#### Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-40°C To +80°C

#### Mechanical Characteristics

Flex Cycle Rating:	1 Million
Bulk Cable Weight:	13 lbs/1000ft
Max. Pull Tension:	22 lbs
Min. Bend Radius (Continuous Flexing):	3 in
Min. Bend Radius/Minor Axis:	1.5 in

#### Standards

UL AWM Style Compliance:	AWM 1354
CSA AWM Compliance:	AWM I/II A/B

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

#### Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT1
UL voltage rating:	30 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

#### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	UPC
7501A G7X1000	Blue, Matte	Reel	1,000 ft	612825187226

Footnote: C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

## History

Update and Revision:

Revision Number: 0.384 Revision Date: 04-08-2022

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.