



Product: [7503A](#)

MachFlex™, Vision Coax 75Ω, #20 Str BC, PO Ins, OA TC Brd, PVC Jkt, AWM 1354

[Request Sample](#)

Product Description

MachFlex™ for High Flex, 1 Conductor 20AWG (105(7x15)x40) Bare Copper, PO Insulation, Overall Tinned Copper Braid(95%) Shield, PVC Outer Jacket, AWM 1354

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	7x15x40	BC - Bare Copper	0.04 in	1

Conductor Count: 1

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.185 in

Outer Shield

Type	Material	Coverage [%]
French Braid	Tinned Copper (TC)	95%

Outer Jacket

Material	Material Trade Name	Nominal Diameter
PVC - Polyvinyl Chloride	Belflex®	0.275 in

Electrical Characteristics

Conductor DCR		
Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
8.1 Ohm/1000ft	11 Ohm/1000ft	11 Ohm/1000ft
Capacitance		
Nom. Capacitance Conductor to Shield		
17.3 pF/ft		
Inductance		
Nominal Inductance		
0.097 µH/ft		
Impedance		
Nominal Characteristic Impedance		
75 Ohm		
High Frequency (Nominal/Typical)		
Frequency [MHz]	Nom. Insertion Loss	
2.2 MHz	0.3 dB/100ft	
5 MHz	0.4 dB/100ft	

10 MHz	0.6 dB/100ft
30 MHz	1.1 dB/100ft
50 MHz	1.5 dB/100ft
100 MHz	2.2 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.3 ns/ft	80%

High Frequency

Frequency [MHz]
2.2 MHz
5 MHz
10 MHz
30 MHz
50 MHz
100 MHz

Voltage

UL Voltage Rating
30 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temperature Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	34 lbs/1000ft
Max. Pull Tension:	35 lbs
Min. Bend Radius (Continuous Flexing):	5.5 in
Min. Bend Radius/Minor Axis:	2.75 in

Standards

UL AWM Style Compliance:	AWM 1354
CSA AWM Compliance:	AWM I/II A/B

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL voltage rating:	30 V RMS
--------------------	----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
7503A G7X500	Blue, Matte	Reel	500 ft	612825187325
7503A G7X1000	Blue, Matte	Reel	1,000 ft	612825187301

Footnote:	C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

History

Update and Revision:	Revision Number: 0.393 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.