

Product: [79007FE](#) 

Life Cycle Status: Capability



Safe-T-Line® 2 x 4.0 mm² Str BC, OS, LSZH, BS6387 CWZ, LPCB

Product Description

Safe-T-Line 2 x 4.0 mm² Stranded BC Fire resistant LPCB approved Multi-conductor, BS 6387 CWZ, EN 50200 PH120+Annex E, IEC60331-2 , Shielded, Silicone Rubber insulation, Low Smoke Zero Halogen Jacket

Technical Specifications

Product Overview

Suitable Applications:	Circuit integrity, Intercom/PA Systems, Sound/Audio Systems, Control Systems, Fire Alarm Systems, Voice Evacuation Systems, Emergency & Safety Systems
------------------------	--

Product Life Cycle

Life Cycle:	Capability - the product is not yet standardly available for orders but can be manufactured
-------------	---

Construction Details

Conductor

No. of Elements	Size	Stranding	Material
2	4 mm ²	Stranded	BC - Bare Copper

Insulation

Material	Nom. Thickness	Color Code	Notes
Silicone Rubber	0.8 mm (0.031 in)	Brown, Blue	BS7655 EI2

Outer Shield

Shield Type	Material	Coverage	Notes
Tape	Bi-Laminate (Alum+Poly)	100%	Drainwire 0.8mm tinned copper

Outer Shield Table Notes:	Tape bonded to sheath
---------------------------	-----------------------

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	11.4 mm (0.449 in)

Outer Jacket1 Table Notes:	COO printed on cable jacket
----------------------------	-----------------------------

Overall Cable Diameter (Nominal):	11.4 mm (0.449 in)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)
4.61 Ohm/km (1.41 Ohm/1000ft)	100 pF/m (30 pF/ft)	165 pF/m (50.3 pF/ft)

Voltage

Voltage Rating
300/500 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +90°C	0°C To +70°C	-40°C To +90°C

Bend Radius

Installation Min.
68 mm (2.7 in)

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-24, IEC 60332-3-25, IEC 60331-2, EN50200 PH30, PH60,PH120. EN50200 Annex E30, BS6387:2013 CWZ
CENELEC Compliance:	EN 60228
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = IEC 60754-1, IEC 61034-2 - Smoke Density Min. Transmittance = 60%
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2)
UK Regulation Compliance:	UKCA Mark

Product Notes

Notes:	BS6387 CWZ: C- Fire @ 950°C - 180min, W - Fire & water @ 650°C - 15 + 15 min.,Z - Fire & mechanical shocks @ 950°C -15 min. Country of Origin printed on the jacket. This is a preliminary Technical Design Specification (TDS). The minimum business quantity to offer is 6km for the first order. This product will have Red as standard color and 500mt as standard put-ups. Additional options for colors and put-ups are available on special request. The estimated production lead time for the first order will be similar to the production lead time of 79001FS. Please liaise with your Belden representative for confirmation.
--------	--

History

Update and Revision:	Revision Number: 0.23 Revision Date: 10-07-2026
----------------------	---

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.