



Product: [76018WS](#)

MachFlex™, 18 C #28 Str TC, SRPVC Ins, OS+TC Srv, PVC Jkt, CMG

[Request Sample](#)

Product Description

MachFlex™ for High Flex, 18 Conductor 28AWG (7x36) Tinned Copper, SRPVC Insulation, Overall Beldfoil®+Tinned Copper Serve(90%) Shield, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	Robotics, Robot, Continuous Flex
------------------------	----------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	18	28	7x36	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.010 in (0.25 mm)	0.035 in (0.89 mm)	Black, Red, White, Green, Orange, Blue, Brown, Yellow, Violet, Slate, Pink, Tan, Red/Green, Red/Yellow, Red/Black, White/Black, White/Red, White/Green

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	26 AWG (7x34) TC
Spiral Serve / Screen	Tinned Copper (TC)	90%	

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Paper Tape	PVC - Polyvinyl Chloride	0.040 in (1.0 mm)	0.282 in

Overall Cable Diameter (Nominal):	0.282 in (7.16 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
67 Ohm/1000ft	25 pF/ft (82 pF/m)	1 Amps per Conductor at 25°C

Voltage

UL Voltage Rating	Voltage Rating
300 V (AWM 2661)	300 V (CSA AWM I/II A/B)

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-10°C To 105°C (Static), 5°C To 105°C (Flexing)

Bend Radius

Flexing Min.

2.3 in (58 mm)

Max. Pull Tension:	31 lbs (14 kg)
Bulk Cable Weight:	51 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 UL loading, FT4
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2661, AWM 10002, AWM I/II A/B
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.145 Revision Date: 05-31-2024
----------------------	--

Part Numbers**Variants**

Item #	Color	Putup Type	UPC
76018WS 008100	Gray	Reel	612825410492
76018WS 0081000	Gray	Reel	612825410508

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.