



**Product:** [76504TS](#)

MachFlex™, 4 Pr #26 Str TC, SRPVC Ins, OS+TC Brd, PVC Jkt, CMG

[Request Sample](#)

## Product Description

MachFlex™ for High Flex, 4 Pair 26AWG (7x34) Tinned Copper, SRPVC Insulation, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, PVC Outer Jacket, CMG

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
26	7x34	TC - Tinned Copper	4

Conductor Count:	8
Total Number of Pairs:	4

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.039 in	0.010 in

#### Outer Shield Material

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	100%	TC - Tinned Copper	26
Braid	Tinned Copper (TC)	85%		

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.272 in	0.040 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
42 Ohm/1000ft	3.2 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor
23 pF/ft

#### Inductance

Nominal Inductance
.20 µH/ft

#### Impedance

Nominal Characteristic Impedance
83 Ohm

#### Voltage

UL Voltage Rating

300 V

## Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-10°C To 105°C (Static), 5°C To 105°C (Flexing)

## Mechanical Characteristics

Flex Cycle Rating:	6 Million Cycles
Bulk Cable Weight:	44 lbs/1000ft
Max. Pull Tension:	24.9 lbs
Min Bend Radius (Continuous Flexing):	4.1 in
Min Bend Radius/Minor Axis:	2.7 in

## Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	AWM 2661, AWM 10002
CSA AWM Compliance:	AWM I/II A/B

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

## Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

## Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT4
UL voltage rating:	300 V RMS

## Part Number

### Variants

Item #	Color	Putup Type	UPC
76504TS 008100	Gray	Reel	612825411383
76504TS 0081000	Gray	Reel	612825411390
76504TS 008500	Gray	Reel	612825411406

## History

Update and Revision:	Revision Number: 0.58 Revision Date: 09-30-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.