



**Part Number: 7732A**

Serial Digital Coax, RG11, #14 Solid BC, Foil + 95% TC braid, CMP

## Product Description

Low Loss Serial Digital Coax, Plenum-CMP, RG11 14 AWG solid bare copper conductor, foam FEP core, Duofoil®, +95% tinned copper braid, fluorocopolymer jacket

## Technical Specifications

### Product Overview

Environmental Space:	Indoor/Outdoor
----------------------	----------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	BC - Bare Copper	0.064 in	1

Conductor Count:	1
------------------	---

#### Insulation

Material	Material Trade Name	Nominal Diameter
FFEP - Foam Fluorinated Ethylene Propylene	Teflon®	0.274 in

#### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum/Polyester/Aluminum	Duofoil®	100 %
Braid	2	TC - Tinned Copper		95 %

#### Outer Jacket Material

Material	Nominal Diameter
PVDF - Fluorocopolymer	0.348 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
2.5 Ohm/1000ft	1.6 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
16.3 pF/ft

#### Inductance

Nominal Inductance
0.091 μH/ft

#### Impedance

Nominal Characteristic Impedance
75 Ohm

#### Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.15 dB/100ft
3.58 MHz	0.26 dB/100ft
5 MHz	0.3 dB/100ft
7 MHz	0.34 dB/100ft
10 MHz	0.4 dB/100ft
67.5 MHz	1.2 dB/100ft
71.5 MHz	1.24 dB/100ft
88.5 MHz	1.4 dB/100ft
100 MHz	1.5 dB/100ft
135 MHz	1.55 dB/100ft
143 MHz	1.65 dB/100ft
180 MHz	1.83 dB/100ft
270 MHz	2.31 dB/100ft
360 MHz	2.76 dB/100ft
540 MHz	3.57 dB/100ft
720 MHz	4.32 dB/100ft
750 MHz	4.44 dB/100ft
1000 MHz	5.42 dB/100ft
1500 MHz	7.06 dB/100ft
2000 MHz	8.57 dB/100ft
2500 MHz	9.93 dB/100ft
3000 MHz	11.27 dB/100ft
4500 MHz	14.67 dB/100ft
6000 MHz	17.86 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.22 ns/ft	83 %

#### Voltage

##### UL Voltage Rating

300 V RMS

Electrical Characteristics Notes: Return Loss: Fixed bridge and termination

#### Temperature Range

Operating Temp Range:	-20°C To +125°C
-----------------------	-----------------

#### Mechanical Characteristics

UV Resistance:	No
Bulk Cable Weight:	83 lbs/1000ft
Max Recommended Pulling Tension:	145 lbs
Min Bend Radius/Minor Axis:	3.5 in

#### Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
RG Type:	11/U Type

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	No

## Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Part Number

Non-Plenum Number:	7731A
--------------------	-------

## Variants

Item #	Color	UPC	Length	Footnote
7732A 0101000	Black	612825188858	1,000 ft	C
7732A 0101200	Black	612825438250	1,200 ft	
7732A 010500	Black	612825188872	500 ft	C
7732A 0101000	Black	612825188858	1,000 ft	C
7732A 0061000	Blue, Light	612825188841	1,000 ft	C
7732A 8771000	Natural	612825188889	1,000 ft	C
7732A 877500	Natural	612825188896	500 ft	C
7732A 0041000	Yellow	612825188834	1,000 ft	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Print legend includes sequential footage marks.
--------	-------------------------------------------------

## History

Update and Revision:	Revision Number: 0.300 Revision Date: 08-22-2019
----------------------	--------------------------------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.