



**Product:** [7769ELV](#)

Cat 7A Cable, S/FTP, LSZH, 4 Pair, AWG 22, Indoor CPR B2ca

## Product Description

CAT7A (1600MHz), 4-Pair, S/FTP shielded, Premise Horizontal Cable, 22 AWG solid bare copper conductors, Foam Polyolefin insulation, each pair with Beldfoil® shield, overall tinned copper braid shield (50% coverage), LSZH jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 6a, 7 and 7a applications: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a> .

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
22	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

#### Insulation

Type	Material	Nominal Diameter
Dielectric	PO - Polyolefin (Foam)	1.6 mm

Bonded-Pair:	No
--------------	----

#### Color Chart

Number	Color
Pair 1	White & Blue
Pair 2	White & Orange
Pair 3	White & Green
Pair 4	White & Brown

#### Inner Shield Material

Type	Material	Coverage [%]
Tape	Bi-Laminate (Alum+Poly)	100%

Table Notes:	Aluminum facing outside
--------------	-------------------------

#### Outer Shield Material

Type	Material	Coverage [%]
Braid	Tinned Copper (TC)	50%

#### Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	8.3 mm	0.3 mm	Yes

### Construction and Dimensions

Min Elongation at Breakof Conductors:	10.0 %
---------------------------------------	--------

Min Elongation at Breakof Insulation:	100.0 %
Min Elongation at Breakof Jacket:	100.0 %
Min Tensile Strength of Jacket:	9 MPa

## Electrical Characteristics

### Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]	Max. DCR Unbalanced Within Pair [%]
95 Ohm/km	4 %	2 %

### Capacitance

Max. Capacitance Unbalance	Max. Mutual Capacitance
1,600 pF/m	56 pF/m

### Impedance

Nominal Characteristic Impedance
100 Ohm

### Delay

Max. Delay Skew
25 ns/100m

### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	78 dB	75 dB	75.9 dB	72.9 dB	78 dB	75 dB	20 dB	67 dB	67 dB	40 dB	23 dB
4 MHz	3.7 dB/100m	78 dB	75 dB	74.3 dB	71.3 dB	78 dB	75 dB	23 dB	67 dB	67 dB	34 dB	15 dB
10 MHz	5.8 dB/100m	78 dB	75 dB	72.2 dB	69.2 dB	75.3 dB	72.3 dB	25 dB	67 dB	67 dB	30 dB	10.9 dB
16 MHz	7.3 dB/100m	78 dB	75 dB	70.7 dB	67.7 dB	71.2 dB	68.2 dB	25 dB	67 dB	67 dB	28 dB	5.1 dB
31.2 MHz	10.3 dB/100m	78 dB	75 dB	67.7 dB	64.7 dB	65.4 dB	62.4 dB	23.6 dB	67 dB	63.3 dB	25.2 dB	
62.5 MHz	14.6 dB/100m	78 dB	75 dB	63.4 dB	60.4 dB	59.4 dB	56.4 dB	21.5 dB	67 dB	57.3 dB	22 dB	
100 MHz	18.5 dB/100m	72.5 dB	69.5 dB	56.9 dB	46.3 dB	55.3 dB	48.5 dB	18.8 dB	67 dB	53.2 dB	18.1 dB	
250 MHz	29.7 dB/100m	69.4 dB	66.4 dB	39.7 dB	36.7 dB	47.3 dB	44.3 dB	17.3 dB	67 dB	45.2 dB	16 dB	
500 MHz	42.8 dB/100m	64.9 dB	61.9 dB	22.2 dB	19.2 dB	41.3 dB	38.3 dB	17.3 dB	67 dB	39.2 dB		
600 MHz	47.1 dB/100m	63.7 dB	60.7 dB	16.6 dB	13.6 dB	39.7 dB	36.7 dB	17.3 dB	65.8 dB	37.6 dB		
1000 MHz	61.9 dB/100m	60.4 dB	57.4 dB			35.3 dB	32.3 dB	15.1 dB	62.5 dB	33.2 dB		
1200 MHz	68.4 dB/100m	59.2 dB	56.2 dB			33.7 dB	30.7 dB	14.3 dB				
1600 MHz	80.0 dB/100m	57.3 dB	54.3 dB			31.2 dB	28.2 dB	13.0 dB				

Table Notes: Limits below 4 MHz and above 1000 MHz are for information only. Reference standard: IEC 61156-5

General Electrical Parameters Notes: Reference standard: ISO/IEC 61156-5

Coupling Attenuation Class: Type I

Segregation class according EN50174-2: d

### Transfer Impedance

Frequency [MHz]	Description	Transfer Impedance
1 Mhz	Grade 1	Max. 10 mOhm/m
10 Mhz		Max. 10 mOhm/m
30 Mhz		Max. 30 mOhm/m
100 Mhz		Max. 100 mOhm/m

### Current

Max. Recommended Current [A]
1.5 Amps per Conductor

### Voltage

Voltage Rating [V]
72 V

## Temperature Range

Installation Temp Range:	0°C To +50°C
Operating Temp Range:	-30°C To +60°C

## Mechanical Characteristics

Bulk Cable Weight:	83 kg/km
Max. Pull Tension:	105 N
Min Bend Radius During Installation:	65 mm
Min Bend Radius During Operation:	33 mm

## Standards

IEC Compliance:	ISO/IEC 11801-1
CPR Euroclass:	B2ca-s1a,d1,a1
CENELEC Compliance:	EN 50173-1
Data Category:	Category 7A
ANSI Compliance:	ANSI/TIA 568.2-D (2018)
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3, Type 4

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass B2ca
----------------------	-------------------------

## Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
Burning Load:	900 kJ/m
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	IEC 61034-2

## Part Number

### Variants

Item #	Color	Putup Type	Length	EAN
7769ELV.00500	Blue	Reel	500 m	8719605161734

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.
--------	--

## History

Update and Revision:	Revision Number: 0.52 Revision Date: 09-30-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.