

1 MHz	2 dB/100m	65.3 dB	62.3 dB	63 dB	60 dB	63.8 dB	60.8 dB	20 dB	23 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	51 dB	49 dB	51.7 dB	48.7 dB	23 dB	23 dB	100 ± 15 Ohm	100 ± 15
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46 dB	43 dB	45.7 dB	42.7 dB	24.5 dB	24.5 dB	100 ± 15 Ohm	100 ± 15
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43 dB	41 dB	43.8 dB	40.8 dB	25 dB	25 dB	100 ± 15 Ohm	100 ± 15
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	39 dB	36 dB	39.7 dB	36.7 dB	25 dB	25 dB	100 ± 15 Ohm	100 ± 15
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.7 dB	34.7 dB	25 dB	25 dB	100 ± 15 Ohm	100 ± 15
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	24.3 dB	24.3 dB	100 ± 15 Ohm	100 ± 15
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31 dB	28 dB	33.9 dB	30.9 dB	23.6 dB	23.6 dB	100 ± 15 Ohm	100 ± 15
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	22 dB	19 dB	27.8 dB	24.8 dB	21.5 dB	21.5 dB	100 ± 15 Ohm	100 ± 15
100 MHz	22 dB/100m	35.3 dB	32.3 dB	14 dB	11 dB	23.8 dB	20.8 dB	20.1 dB	20.1 dB	100 ± 15 Ohm	

Voltage

Non-UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +75°C	-25°C To +75°C	-40°C To +85°C

Bend Radius

Stationary Min.
2.75 in

Max. Pull Tension:	40 lbs
Bulk Cable Weight:	33 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor - Direct Burial, Outdoor, Non-Halogenated, Sunlight Resistance, Oil Resistance
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
CPR Euroclass:	Fca
European Directive Compliance:	EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
7937A 0101000	Black	Reel	1,000 ft	612825191728

Product Notes

Notes:	Operating temperatures are subject to length de-rating. Cable passes -40°C Cold Bend per UL 1581. Sequential marking at two foot intervals. Polymer gel waterblocking material.
--------	---

History

Update and Revision:	Revision Number: 0.377 Revision Date: 09-30-2020
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.