

Part Number: 7938A

DataTuff® Cat 5e, (4 pr) 24 AWG (7x32) CA, PO/TPE/TPE, Foil+TC Braid Shld, Upjacketed, Weld Spatter Res, 10M Flex



Product Description

Four Cat 5e 24 AWG Bonded Pairs stranded (7x32) bare copper alloy conductors, polyolefin insulation, TPE inner jacket, Beldfoil® shield (100% coverage) plus tinned copper braid (85% coverage), weld spatter resistant TPE jacket, 10 million flex life cycles.

Technical Specifications

Product Overview

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, Robotic Applications, Flexible Applications, 100MHz Category 5e, Industrial Patch Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, CMX - Outdoor, RJ-45 Compatible*
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	CA - Copper Alloy	4

Total Number of Conductors:	8
-----------------------------	---

Insulation

Material
PO - Polyolefin

Color Chart

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Inner Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
TPE	0.254 in	0.02 in

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Nominal Diameter
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	
Braid	TC - Tinned Copper		85 %	0.282 in

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord	Separator Material
Industrial Grade TPE - Thermoplastic Elastomer	0.342 in	0.03 in	No	Polyester

Electrical Characteristics

Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance
330 pF/ft	15 pF/ft

Shielding:	Al/Foil + Braid
------------	-----------------

Construction and Dimensions

Total Number of Pairs:	4
------------------------	---

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
11 Ohm/1000ft	3 %

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
510 ns/100m	45 ns/100m	69 %	12 ns/ft

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.5 dB/100m	65.3 dB	62.3 dB	62.8 dB	59.8 dB	63.8 dB	60.8 dB	20 dB	23 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	4.9 dB/100m	56.3 dB	53.3 dB	51.4 dB	48.4 dB	51.7 dB	48.7 dB	23 dB	23 dB	100 ± 15 Ohm	100 ± 15 Ohm
8 MHz	6.9 dB/100m	51.8 dB	48.8 dB	44.9 dB	41.9 dB	45.7 dB	42.7 dB	24.5 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
10 MHz	7.8 dB/100m	50.3 dB	47.3 dB	42.5 dB	39.5 dB	43.8 dB	40.8 dB	25 dB	25 dB	100 ± 15 Ohm	100 ± 15 Ohm
16 MHz	9.9 dB/100m	47.3 dB	44.3 dB	37.4 dB	34.4 dB	39.7 dB	36.7 dB	25 dB	25 dB	100 ± 15 Ohm	100 ± 15 Ohm
20 MHz	11.1 dB/100m	45.8 dB	42.8 dB	34.7 dB	31.7 dB	37.7 dB	34.7 dB	25 dB	25 dB	100 ± 15 Ohm	100 ± 15 Ohm
25 MHz	12.5 dB/100m	44.3 dB	41.3 dB	21.8 dB	28.8 dB	35.8 dB	32.8 dB	24.3 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm
31.25 MHz	14.1 dB/100m	42.9 dB	39.9 dB	28.8 dB	25.8 dB	33.9 dB	30.9 dB	23.6 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm
62.5 MHz	20.4 dB/100m	38.4 dB	35.4 dB	18 dB	15 dB	27.8 dB	24.8 dB	21.5 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
100 MHz	26.4 dB/100m	35.3 dB	32.3 dB	8.9 dB	5.9 dB	23.8 dB	20.8 dB	20.1 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm

Voltage

UL Voltage Rating
300V RMS

Applicable Standards & Environmental Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CPR Euroclass:	Eca
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Patent:	http://www.belden.com/p

Standards

ISO/IEC Compliance:	Other Standards
ANSI/TIA Category:	Category 5e

Flame Test

C(UL) Flammability:	FT1
UL Flammability:	UL1581 Vertical Tray (VW-1)

Safety

UL Voltage Rating:	300V RMS
--------------------	----------

Suitability

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

Mechanical Characteristics

Storage Temp Range:	-40°C To +80°C
Installation Temp Range:	-25°C To +75°C
Operating Temp Range:	-40°C To +80°C
Bulk Cable Weight:	60(lbs/1000ft)
Max Recommended Pulling Tension:	40(lbs)
Min Bend Radius/Minor Axis:	3.5(in)

Temperature Range

UL Temp Rating:	60°C
-----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

History

Variants

Item #	Color
7938A B59500	BLACK, MATTE
7938A B591000	MATTE BLACK

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.