



Product: [77807WS](#)

MachFlex™, 7+G C #18 Str BC, PVC Ins, OA TC Brd, PVC Jkt, PVC Jkt, AWM 2587

[Request Sample](#)

Product Description

MachFlex™ for High Flex, 7+G Conductor 18AWG (105(7x15)x38) Bare Copper, PVC Insulation, Overall Tinned Copper Braid(85%) Shield, PVC Inner Jacket, PVC Outer Jacket, AWM 2587

Technical Specifications

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	6	18	105x38	BC - Bare Copper
Ground	1	18	105x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.096 in (2.4 mm)	Red and Numbered
Ground	PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.096 in (2.4 mm)	Yellow/Green/Green

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	85%

Inner Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Tissue Tape	PVC - Polyvinyl Chloride	0.030 in (0.76 mm)	0.408 in (10.4 mm)

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Tissue Tape	PVC - Polyvinyl Chloride	0.045 in (1.1 mm)	0.532 in

Overall Cable Diameter (Nominal): 0.532 in (13.5 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	6.4 Ohm/1000ft	45 pF/ft (150 pF/m)	9.8 Amps per Conductor at 30°C
Ground Wire	6.66 Ohm/1000ft (21.9 Ohm/km)		

Voltage

UL Voltage Rating	Voltage Rating
600 V (AWM 2587)	600 V (CSA AWM I/II A/B)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C	-40°C To 90°C (Static), -5°C To 90°C (Flexing)

Bend Radius

Flexing Min.

4.3 in (110 mm)

Max. Pull Tension:	105 lbs (47.6 kg)
Bulk Cable Weight:	344 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Oil Resistance
Flammability / Reaction to Fire:	FT1
AWM Compliance:	AWM 2587, AWM 10012, AWM I/II A/B
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	VDE 0472, Section 803 Oil Test

History

Update and Revision:	Revision Number: 0.136 Revision Date: 04-08-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	UPC
77807WS 010100	Black	Reel	612825412403
77807WS 0101000	Black	Reel	612825412410

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.