


## Part Number: 7958A



DataTuff® Cat 5e, (4 pr) 24 AWG Solid BC, PO/PVC, Foil Shld, EtherNet/IP, CMR, 600 V AWM, MSHA

### Product Description

Four Cat 5e 24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield (100% coverage), industrial grade oil- and UV-resistant PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, 200MHz Category 5e, Industrial Ethernet, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, CMX - Outdoor, RJ-45 Compatible*
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
AWG Size:	24

##### Insulation

Material	Nominal Wall Thickness
PO - Polyolefin	0.01 in

##### Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

##### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

##### Outer Jacket Material

Material	Nominal Diameter	Ripcord
Industrial Grade PVC - Polyvinyl Chloride	0.265 in	No

#### Electrical Characteristics

##### Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
9.38 Ohm/1000ft	3 %

##### Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
150 pF/ft	15 pF/ft

##### Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]

538 ns/100m	45 ns/100m	70 %
-------------	------------	------

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)
1 MHz	2 dB/100m	65.3 dB	62.3 dB	63 dB	60 dB	63.8 dB	60.8 dB	20 dB	20 dB	100 ± 15 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	51 dB	49 dB	51.7 dB	48.7 dB	23.6 dB	23.6 dB	100 ± 15 Ohm
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46 dB	43 dB	45.7 dB	42.7 dB	25.4 dB	25.4 dB	100 ± 15 Ohm
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43 dB	41 dB	43.8 dB	40.8 dB	26 dB	26 dB	100 ± 15 Ohm
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	39 dB	36 dB	39.7 dB	36.7 dB	26 dB	26 dB	100 ± 15 Ohm
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.7 dB	34.7 dB	26 dB	26 dB	100 ± 15 Ohm
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	25.5 dB	25.5 dB	100 ± 15 Ohm
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31 dB	28 dB	33.9 dB	30.9 dB	25 dB	25 dB	100 ± 15 Ohm
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	22 dB	19 dB	27.8 dB	24.8 dB	23.5 dB	23.5 dB	100 ± 15 Ohm
100 MHz	22 dB/100m	35.3 dB	32.3 dB	14 dB	11 dB	23.8 dB	20.8 dB	22.5 dB	22.5 dB	100 ± 15 Ohm
200 MHz	32.4 dB/100m		27.8 dB		1 dB		14.7 dB			100 ± 25 Ohm
1 MHz										
4 MHz										
8 MHz										
10 MHz										
16 MHz										
20 MHz										
25 MHz										
31.25 MHz										
62.5 MHz										
100 MHz										
200 MHz										

#### Voltage

UL Description	UL Voltage Rating
	300V RMS
Appliance Wiring Material	600 V RMS

#### Temperature Range

Installation Temp Range:	-25°C To +75°C
UL Temp Rating:	60°C
Storage Temp Range:	-40°C To +75°C
Operating Temp Range:	-40°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	32 lbs/1000ft
Max Recommended Pulling Tension:	35 lbs
Min Bend Radius/Minor Axis:	0.5 in

#### Standards

NEC/(UL) Specification:	CMR, CMX-OUTDOOR, UL 444
CEC/C(UL) Specification:	CMR
UL AWM Style:	UL Style 21047
ISO/IEC Compliance:	ISO/IEC 11801 ed 2.1 (2008) Class D
CPR Euroclass:	Eca
Data Category:	Category 5e
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e, UL verified to Category 5e, Ethernet/IP™ Compliant

#### Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65 (CJ for Wire & Cable):	Yes

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

## Suitability

Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Riser
CSA Flammability:	FT4

## Part Number

Plenum (Y/N):	No
---------------	----

## Variants

Item #	Color	Footnote
7958A 0101000	BLACK	C
7958A 0102000	BLACK	
7958A 0061000	BLUE	C
7958A 0061000	BLUE	C
7958A 0081000	GRAY	C
7958A 0021000	RED	C
7958A 1NH1000	TEAL	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	<a href="http://www.belden.com/p">http://www.belden.com/p</a>

## Product Notes

Notes:	US Patent #'s 5,606,151; 5,734,126. EtherNet/IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vender Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. *Special RJ45 plug required. See WWW. BELDEN.COM - Tools - Connector Cross Reference. Not intended for 600 V electrical power delivery.
--------	--

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.