



Product: [7805](#)

50 Ohm Wireless Transmission Coax, RF 100, RG174, 25 AWG Solid BC, Foil + 90% TC Braid, PVC Jkt

Product Description

50 Ohm Wireless Transmission Coax, RF 100, RG174, 25 AWG Solid Bare Copper Conductor, PE Insulation, Beldfoil® + 90% Tinned Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

Construction Details

RG Type:	174
----------	-----

Conductor

Size	Stranding	Nom. Diameter	Material
25 AWG	Solid	0.018 in	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.061 in (1.5 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%
2	Braid	Tinned Copper (TC)		90%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.110 in (2.79 mm)

Overall Cable Diameter (Nominal):	0.110 in (2.79 mm)
-----------------------------------	--------------------

Electrical Characteristics

VSWR

Frequency	Max. VSWR
5 - 6000 MHz	1.25:1

Attenuation

Frequency	Nom. Attenuation	Max. Attenuation
5 MHz	1.5 dB/100ft	
10 MHz	2.2 dB/100ft	
30 MHz	3.8 dB/100ft	3.9 dB/100ft
50 MHz	4.9 dB/100ft	5.1 dB/100ft
150 MHz	8.6 dB/100ft	8.8 dB/100ft
220 MHz	10.4 dB/100ft	10.7 dB/100ft
450 MHz	15.2 dB/100ft	15.5 dB/100ft

900 MHz	22.0 dB/100ft	22.5 dB/100ft
1500 MHz	28.7 dB/100ft	30.2 dB/100ft
1800 MHz	31.7 dB/100ft	33.5 dB/100ft
2000 MHz	33.4 dB/100ft	35.6 dB/100ft
2500 MHz	37.8 dB/100ft	40.8 dB/100ft
3000 MHz	42.0 dB/100ft	45.8 dB/100ft
3500 MHz	45.4 dB/100ft	49.5 dB/100ft
4500 MHz	52.3 dB/100ft	56.8 dB/100ft
5800 MHz	60.9 dB/100ft	64.3 dB/100ft
6000 MHz	62.0 dB/100ft	65.4 dB/100ft

Power Rating

Frequency	Max. Power Rating
30 MHz	216 W
50 MHz	154 W
150 MHz	74 W
220 MHz	57 W
450 MHz	34 W
900 MHz	21 W
1,500 MHz	14 W
2,000 MHz	12 W
2,500 MHz	10 W
3,500 MHz	8 W
4,500 MHz	7 W
6,000 MHz	5 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
32 Ohm/1000ft	9.1 Ohm/1000ft (30 Ohm/km)	31.2 pF/ft (102 pF/m)	50 Ohm	66%

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating
-40°C to +75°C

Bend Radius

Installation Min.
0.25 in (6.4 mm)

Max. Pull Tension:	16 lbs (7.3 kg)
Bulk Cable Weight:	9 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.481 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7805 010100	Black	Reel	100 ft	612825189527	E
7805 010500	Black	Reel	500 ft	612825189541	
7805 0101000	Black	Reel	1,000 ft	612825189534	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.