




Product: [7988R](#)



Low Skew, Category 5e, 4-24 AWG pairs, CMR

Product Description

Category 5e, 24 AWG bonded pairs solid bare copper conductors, non-plenum, polyolefin insulation, skew 9.0ns/100m nominal, rip cord, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	Category 5e, UTP Based Video Applications, and KVM
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.204 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
90 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
66	15 pF/ft

Delay

Max. Delay	Nominal Velocity of Propagation (VP) [%]
0.027 ns/ft	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	65.3 dB	65.3 dB	60.3 dB	60.3 dB	63.8 dB	60.8 dB	20 dB	100 ± 15	100 ± 15
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	49.2 dB	49.2 dB	51.7 dB	48.7 dB	23 dB	100 ± 15	100 ± 15
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	43 dB	43 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 15	100 ± 15
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	40.8 dB	40.8 dB	43.8 dB	40.8 dB	25 dB	100 ± 15	100 ± 15
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	36 dB	36 dB	39.7 dB	36.7 dB	25 dB	100 ± 15	100 ± 15
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	33.5 dB	33.5 dB	37.7 dB	34.7 dB	25 dB	100 ± 15	100 ± 15
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	30.9 dB	30.9 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15	100 ± 15
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	28.2 dB	28.2 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15	100 ± 15
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	18.4 dB	18.4 dB	27.8 dB	24.8 dB	21.5 dB	100 ± 15	100 ± 15
100 MHz	22 dB/100m	35.3 dB	32.3 dB	10.3 dB	10.3 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 15	100 ± 15
155 MHz	28.1 dB/100m	32.5 dB	29.5 dB	2 dB	2 dB	19.9 dB	16.9 dB	15.8 dB	100 ± 25	100 ± 15
200 MHz	32.4 dB/100m	30.8 dB	27.8 dB	1 dB	1 dB	17.7 dB	14.7 dB	15 dB	100 ± 25	100 ± 15

Voltage

UL Description	UL Voltage Rating
CMR	300 V

Temperature Range

Operating Temperature Range:	-20°C To +75°C
------------------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	20 lbs/1000ft
Max. Pull Tension:	40 lbs
Min. Bend Radius/Minor Axis:	0.25 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
ISO/IEC Compliance:	11801 Category 5
CPR Euroclass:	Eca
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	7988P

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
7988R N3UU1000	Green, Mil	UnReel	1,000 ft	612825192558

Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5e.
--------	--

History

Update and Revision:	Revision Number: 0.458 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.