



Product: [7844P](#)

4-Channel SMPTE Stadium Cable, 8 Single Mode Fiber, 8 Conductor 18 AWG and 8 Conductor 24 AWG, Plenum

Product Description

4-Channel SMPTE Stadium Cable, 8 Single Mode Fiber, 8 TC Conductor (19x30) 18 AWG and 8 TC Conductor (7x32) 24 AWG, FEP Insulation, Beldfoil Shield, PVDF Jacket, Plenum

Technical Specifications

Product Overview

Suitable Applications:	4 Channel Composite Camera Cable
------------------------	----------------------------------

Multiconductor

Multiconductor Conductor and Insulation

Element	No. of Conductors	AWG	Stranding	Material	Nominal Conductor DCR	Insulation Material	Insulation Nominal Diameter
Brown Quad, Orange Quad, Green Quad, White Quad	8	24	7x32	TC - Tinned Copper	23.3 Ohm/1000ft Ohm/1000ft	FEP - Fluorinated Ethylene Propylene	0.038 in
Brown Quad, Orange Quad, Green Quad, White Quad	8	18	19x30	TC - Tinned Copper	6.67 Ohm/1000ft	FEP - Fluorinated Ethylene Propylene	0.064 in

Multiconductor Color Chart

Description	Color
Brown Quad - 24 AWG	Red
Brown Quad - 24 AWG	Gray
Brown Quad - 18 AWG	White
Brown Quad - 18 AWG	Black
Orange Quad - 24 AWG	Red
Orange Quad - 24 AWG	Gray
Orange Quad - 18 AWG	White
Orange Quad - 18 AWG	Black
Green Quad - 24 AWG	Red
Green Quad - 24 AWG	Gray
Green Quad - 18 AWG	White
Green Quad - 18 AWG	Black
White Quad - 24 AWG	Red
White Quad - 24 AWG	Gray
White Quad - 18 AWG	White
White Quad - 18 AWG	Black

Multiconductor Inner Shield

Layer	Inner Shield Type	Inner Shield Material	Inner Shield Coverage	Drainwire AWG	Drainwire Stranding	Drainwire Material	Drainwire Diameter	Drainwire Position
All Quads	Tape	Al/poly (Foil in)	100 %	24	7x32	TC - Tinned Copper	0.024 in	Under Shield Tape

Multiconductor Inner Jacket

Element	Material	Nominal Diameter
All Quads	PVDF - Polyvinylidene Fluoride	0.154 in

Multiconductor UL Voltage

UL Description	UL Voltage Rating

24 AWG	300 V RMS
18 AWG	300 V RMS

Fiber

Fiber Color Coding:	TIA-598-D
---------------------	-----------

Buffer Specification

Buffer Material	Buffer Diameter
PVC - Polyvinyl Chloride	900 µm

Number of Active Subunits:	8
Number of Subunit Positions:	8
Fibers Per Subunit:	1
Mode Field Diameter:	9.2 µm
Wavelength@Optical SM1:	1310 nm, 1550 nm
Max. Attenuation at 1310 nm:	0.50 dB/km
Max. Attenuation at 1550 nm:	0.50 dB/km

Overall Cable

Outer Jacket

Nominal Diameter
0.477 in

Jacket:	PVDF
Operating Temperature Range:	0°C to 70°C
Installation Temperature Range:	0°C to 70°C
Storage Temperature Range:	0°C to 70°C
Max. Pull Tension:	800 N
Bulk Cable Weight:	193 lbs/1000ft

Applicable Standards & Environmental Programs

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
Other Standards:	SMPTE 311
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire and Cable):	Yes
China RoHS II (GB/T 26572-2011):	Yes

Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes
UV Resistance:	Yes

Flame Test

UL Flammability:	NFPA 262
------------------	----------

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	7844R

History

Update and Revision:	Revision Number: 0.28 Revision Date: 11-27-2023
----------------------	---

Variants

Item #	Color	Length
7844P 0101000	Black	1,000 ft
7844P 0104000	Black	4,000 ft

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.