



**Part Number:** 8049

Magnet Wire, #18 Sol BC, PUR/NYL Ins, J-W-1177/9 MW 28-C

[Request Sample](#)

**Product Description**

Magnet Wire, 18AWG (Solid) Bare Copper, PUR/NYL Insulation, J-W-1177/9 MW 28-C

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
18	Solid	BC - Bare Copper	1

Conductor Count: 1

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
PUR/Nylon - Polyurethane/Nylon	0.0424 in	0.001 in

**Outer Jacket Material**

Material	Max. Diameter
No Jacket	0.0424 mm

**Construction and Dimensions**

Min Increase in OD: 0.001 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
6.4 Ohm/1000ft

**Current**

Max. Recommended Current [A]
2.3 A

**Voltage**

Breakdown Voltage
2850 volts minimum at room temperature

**Temperature Range**

Non-UL Temp Rating: 130°C

**Mechanical Characteristics**

Approximate Length:	100 ft
Turns Per Linear Inch:	23.9
Turns Per Square Inch:	571
Bulk Cable Weight:	5 lbs/1000ft

## Standards

UL AWM Style:	N/A
Military Specification:	J-W-1177/9
Other Specification:	NEMA-MW28-C (Single)

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

UL voltage rating:	N/A
--------------------	-----

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	UPC	Length
8049	None	612825194453	1 ft

## History

Update and Revision:	Revision Number: 0.276 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.