



Product: [7932A](#)

DataTuff® 5e, 2 Bonded-Pr #24 Sol BC, PO Ins, PVC Jkt, CMR SUN RES OIL RES

Product Description

Industrial Ethernet Cat 5e, 2 Bonded-Pair 24AWG (Solid) Bare Copper, PO Insulation, PVC Outer Jacket, CMR SUN RES OIL RES

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc. |
|------------------------|--|

Physical Characteristics (Overall)

Conductor

| Element | AWG | Stranding | Material | Nominal Diameter | No. of Pairs |
|---------|-----|-----------|------------------|------------------|--------------|
| Pair(s) | 24 | Solid | BC - Bare Copper | 0.02 in | 2 |

| | |
|------------------------|---|
| Conductor Count: | 4 |
| Total Number of Pairs: | 2 |

Insulation

| Element | Material | Nominal Diameter | Nominal Wall Thickness |
|---------|-----------------|------------------|------------------------|
| Pair(s) | PO - Polyolefin | 0.043 in | 0.010 in |

| | |
|--------------|-----|
| Bonded-Pair: | Yes |
|--------------|-----|

Color Chart

| Number | Color |
|--------|-----------------------|
| 1 | Orange & White/Orange |
| 2 | Green & White/Green |

Outer Jacket

| Material | Nominal Diameter | Ripcord |
|--------------------------|------------------|---------|
| PVC - Polyvinyl Chloride | 0.207 in | Yes |

Electrical Characteristics

Conductor DCR

| Max. Conductor DCR | Max. DCR Unbalance |
|--------------------|--------------------|
| 29.7 Ohm/1000ft | 3 % |

Capacitance

| Max. Capacitance Unbalance | Nom. Mutual Capacitance |
|----------------------------|-------------------------|
| 90 pF/100m | 15 pF/ft |

Delay

| Max. Delay | Max. Delay Skew | Nominal Velocity of Propagation (VP) [%] |
|-------------|-----------------|--|
| 510 ns/100m | 25 ns/100m | 70% |

High Frequency

| Frequency [MHz] | Max. Insertion Loss (Attenuation) | Min. NEXT [dB] | Min. PSNEXT [dB] | Min. ACR [dB] | Min. PSACR [dB] | Min. ACRF (ELFEXT) [dB] | Min. PSACRF (PSELFEXT) [dB] | Min. RL (Return Loss) [dB] | Max./Min. Input Impedance (unFitted) | Max./Min. Fitted Impedance |
|-----------------|-----------------------------------|----------------|------------------|---------------|-----------------|-------------------------|-----------------------------|----------------------------|--------------------------------------|----------------------------|
|-----------------|-----------------------------------|----------------|------------------|---------------|-----------------|-------------------------|-----------------------------|----------------------------|--------------------------------------|----------------------------|

| | | | | | | | | | | |
|-----------|--------------|---------|---------|---------|---------|---------|---------|---------|--------------|------------|
| 1 MHz | 2 dB/100m | 65.3 dB | 65.3 dB | 63.3 dB | 63.3 dB | 63.8 dB | 60.8 dB | 20 dB | 100 ± 12 Ohm | 95-110 Ohm |
| 4 MHz | 4 dB/100m | 56.3 dB | 56.3 dB | 52.3 dB | 52.3 dB | 51.7 dB | 48.7 dB | 23.6 dB | 100 ± 12 Ohm | 95-110 |
| 8 MHz | 5.7 dB/100m | 51.8 dB | 51.8 dB | 46.1 dB | 46.1 dB | 45.7 dB | 42.7 dB | 25.4 dB | 100 ± 12 Ohm | 95-107 |
| 10 MHz | 6.4 dB/100m | 50.3 dB | 50.3 dB | 43.9 dB | 43.9 dB | 43.8 dB | 40.8 dB | 26 dB | 100 ± 12 Ohm | 95-107 |
| 16 MHz | 8.1 dB/100m | 47.3 dB | 47.3 dB | 39.1 dB | 39.1 dB | 39.7 dB | 36.7 dB | 26 dB | 100 ± 12 Ohm | 95-107 |
| 20 MHz | 9.2 dB/100m | 45.8 dB | 45.8 dB | 35.2 dB | 35.2 dB | 37.7 dB | 34.7 dB | 26 dB | 100 ± 12 Ohm | 95-107 |
| 25 MHz | 10.3 dB/100m | 44.3 dB | 44.3 dB | 34.1 dB | 34.1 dB | 35.8 dB | 32.8 dB | 25.5 dB | 100 ± 15 Ohm | 95-107 |
| 31.25 MHz | 11.6 dB/100m | 42.9 dB | 42.9 dB | 31.3 dB | 31.3 dB | 33.9 dB | 30.9 dB | 25 dB | 100 ± 15 Ohm | 95-107 |
| 62.5 MHz | 16.8 dB/100m | 38.4 dB | 38.4 dB | 21.6 dB | 21.6 dB | 27.8 dB | 24.8 dB | 23.5 dB | 100 ± 15 Ohm | 95-107 |
| 100 MHz | 21.7 dB/100m | 35.3 dB | 35.3 dB | 17.1 dB | 17.1 dB | 23.8 dB | 20.8 dB | 22.5 dB | 100 ± 15 Ohm | |
| 155 MHz | 27.7 dB/100m | 32.5 dB | 32.5 dB | 4.7 dB | 4.7 dB | 19.9 dB | 16.9 dB | 19 dB | 100 ± 18 Ohm | |
| 200 MHz | 32 dB/100m | 30.8 dB | 30.8 dB | 3 dB | 3 dB | 17.7 dB | 14.7 dB | 19 dB | 100 ± 20 Ohm | |
| 250 MHz | 36.4 dB/100m | 29.3 dB | 29.3 dB | 0 dB | 0 dB | 15.8 dB | 12.8 dB | 18 dB | 100 ± 20 Ohm | |
| 300 MHz | 40.5 dB/100m | 28.2 dB | 28.2 dB | 0 dB | 0 dB | 14.2 dB | 11.2 dB | 18 dB | 100 ± 20 Ohm | |
| 310 MHz | 41.3 dB/100m | 27.9 dB | 27.9 dB | | | 13.9 dB | 10.9 dB | 18 dB | 100 ± 20 Ohm | |
| 350 MHz | 44.3 dB/100m | 27.2 dB | 27.2 dB | | | 12.9 dB | 9.9 dB | 17 dB | 100 ± 22 Ohm | |

Voltage

| |
|--------------------------|
| UL Voltage Rating |
| 300 V RMS |

Temperature Range

| | |
|---------------------------------|----------------|
| Installation Temperature Range: | -25°C To +75°C |
| UL Temp Rating: | 75°C |
| Storage Temperature Range: | -40°C To +85°C |
| Operating Temperature Range: | -40°C To +75°C |

Mechanical Characteristics

| | |
|---------------------------------------|---------------|
| UV Resistance: | Yes |
| Bulk Cable Weight: | 17 lbs/1000ft |
| Max. Pull Tension: | 20 lbs |
| Min. Bend Radius During Installation: | 2.07 in |
| Min. Bend Radius/Minor Axis: | 0.25 in |

Standards

| | |
|---------------------------------------|----------------------|
| NEC Articles: | Article 800 |
| NEC/(UL) Compliance: | CMR |
| CEC/C(UL) Compliance: | CMR |
| ISO/IEC Compliance: | ISO/IEC 11801 Cat 5e |
| CPR Euroclass: | Eca |
| Data Category: | Category 5e |
| TIA/EIA Compliance: | TIA-568.C.2 Cat 5e |
| Third Party Performance Verification: | UL Verified Cat 5e |

Applicable Environmental and Other Programs

| | |
|--|-------------------------------|
| Environmental Space: | Indoor/Outdoor |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| EU Directive 2011/65/EU (RoHS 2): | Yes |
| EU Directive 2012/19/EU (WEEE): | Yes |
| EU Directive 2015/863/EU (RoHS 2 amendment): | Yes |
| EU Directive Compliance: | EU Directive 2003/11/EC (BFR) |
| EU CE Mark: | Yes |
| MII Order #39 (China RoHS): | Yes |

Suitability

| | |
|-------------------------------|-----|
| Suitability - Indoor: | Yes |
| Suitability - Oil Resistance: | Yes |

| | |
|------------------------------------|-----|
| Suitability - Outdoor: | Yes |
| Suitability - Sunlight Resistance: | Yes |

Flammability, LSOH, Toxicity Testing

| | |
|-------------------------|---------------|
| CSA/C(UL) Flammability: | FT4 |
| UL Flammability: | UL1666 Riser |
| IEC Flammability: | IEC 60332-1-2 |
| UL voltage rating: | 300 V RMS |

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Related Part Numbers

Variants

| Item # | Color | Put-Up Type | Length | UPC |
|---------------|-------|-------------|----------|--------------|
| 7932A 0101000 | Black | Reel | 1,000 ft | 612825191612 |
| 7932A 0021000 | Red | Reel | 1,000 ft | 612825191605 |
| 7932A 1NH1000 | Teal | Reel | 1,000 ft | 612825191636 |

| | |
|-----------|------------------------|
| Footnote: | C - CRATE REEL PUT-UP. |
|-----------|------------------------|

Product Notes

| | |
|--------|--|
| Notes: | US Patent #'s 5, 606, 151; 5, 734, 126. EtherNet IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. |
|--------|--|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.540 Revision Date: 04-29-2024 |
|----------------------|--|

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.