

Part Number: 7953A

DataTuff® Cat 6, (4 pr) 23 AWG Solid BC, PP/PVC/PVC, EtherNet/IP, Foil Shld, CMR, CMX, 600 V AWM



Product Description

Four Cat 6 23 AWG Bonded-Pairs solid bare copper conductors, polypropylene insulation, FRPE spline center member, inner PVC jacket, overall Beldfoil® Shield (100% coverage), industrial grade oil- and UV-resistant PVC outer jacket.

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155 ATM, 622 ATM, 250MHz Category 6 |
|------------------------|--|

Physical Characteristics (Overall)

Conductor

| Element | AWG | Stranding | Material | No. of Pairs |
|-----------|-----|-----------|------------------|--------------|
| | 23 | Solid | BC - Bare Copper | 4 |
| No Ground | | | | |

Total Number of Conductors: 8

Insulation

| Material | Nominal Diameter | Nominal Wall Thickness |
|--------------------|------------------|------------------------|
| PP - Polypropylene | 0.043 in | 0.01 in |

Color Chart

| Number | Color |
|--------|------------------------------|
| 1 | White/Blue Stripe & Blue |
| 2 | White/Orange Stripe & Orange |
| 3 | White/Green Stripe & Green |
| 4 | White/Brown Stripe & Brown |

Inner Shield Material

| Type | Material | Material Trade Name | Coverage [%] | Drainwire Material | Drainwire AWG |
|------|------------------------------|---------------------|--------------|--------------------|---------------|
| Tape | Aluminum Foil-Polyester Tape | Beldfoil® | 100 % | TC - Tinned Copper | 24 |

Inner Jacket Material

| Material | Nominal Diameter | Nominal Wall Thickness | Ripcord |
|---|------------------|------------------------|---------|
| Industrial Grade PVC - Polyvinyl Chloride | 0.335 in | 0.02 in | Yes |

Outer Shield Material

| Type | Material | Material Trade Name | Coverage [%] | Drainwire Material | Drainwire AWG | Drainwire Construction n x D |
|------|------------------------------|---------------------|--------------|--------------------|---------------|------------------------------|
| Tape | Aluminum Foil-Polyester Tape | Beldfoil® | 100 % | TC - Tinned Copper | 24 | 7x32 mm |

Outer Jacket Material

| Material | Nominal Diameter | Nominal Wall Thickness | Ripcord |
|---|------------------|------------------------|---------|
| Industrial Grade PVC - Polyvinyl Chloride | 0.695 in | 0.03 in | No |

Electrical Characteristics

Capacitance

| Max. Capacitance Unbalance | Nom.Mutual Capacitance |
|----------------------------|------------------------|
| 330 pF/ft | 15 pF/ft |

Shielding: Beldfoil® Shield

Construction and Dimensions

| | |
|------------------------|---|
| Total Number of Pairs: | 4 |
|------------------------|---|

Stranding

| Lay Length |
|------------|
| N mm |

Print Legend: 7953A BELDEN VERIFIED (UL) CAT 6 4PR23 E108998-M CMR-CMX OUTDOOR OR C(UL) CMG----ISO/IEC11801 CAT 6 --- 300V PATENTED OIL/SUN RES FT4 IEEE 1202 123456 FT

Armor

| Type of Armor | Material |
|---------------|----------|
| Interlocked | Aluminum |

Conductor DCR

| Max. Conductor DCR | Max. DCR Unbalance |
|--------------------|--------------------|
| 8.2 Ohm/1000ft | 3 % |

Delay

| Max. Delay | Max. Delay Skew | Nominal Velocity of Propagation (VP) [%] |
|-------------|-----------------|--|
| 537 ns/100m | 45 ns/100m | 72 % |

High Freq

| Frequency [MHz] | Max. Insertion Loss (Attenuation) | Min. NEXT [dB] | Min. PSNEXT [dB] | Min. ACR [dB] | Min. PSACR [dB] | Min. ACRF (ELFEXT) [dB] | Min. PSACRF (PSELFEXT) [dB] | Min. RL (Return Loss) [dB] | Min. SRL (Structural Return Loss) | Max./Min. Input Impedance (unFitted) | Max./Min. Fitted Impedance |
|-----------------|-----------------------------------|----------------|------------------|---------------|-----------------|-------------------------|-----------------------------|----------------------------|-----------------------------------|--------------------------------------|----------------------------|
| 1 MHz | 2 dB/100m | 74.3 dB | 72.3 dB | 72.3 dB | 70.3 dB | 67.8 dB | 64.8 dB | 21 dB | na dB | 100 ± 15 Ohm | |
| 4 MHz | 3.8 dB/100m | 65.3 dB | 63.3 dB | 61.5 dB | 59.5 dB | 55.8 dB | 52.7 dB | 24 dB | na dB | 100 ± 15 Ohm | |
| 8 MHz | 5.3 dB/100m | 60.8 dB | 58.8 dB | 55.4 dB | 53.4 dB | 49.7 dB | 46.7 dB | 25.5 dB | na dB | 100 ± 15 Ohm | |
| 10 MHz | 6 dB/100m | 59.3 dB | 57.3 dB | 53.3 dB | 51.3 dB | 47.8 dB | 44.8 dB | 26 dB | na dB | 100 ± 15 Ohm | |
| 16 MHz | 7.6 dB/100m | 56.2 dB | 54.3 dB | 48.7 dB | 46.7 dB | 43.7 dB | 40.7 dB | 26 dB | na dB | 100 ± 15 Ohm | |
| 20 MHz | 8.5 dB/100m | 54.8 dB | 52.8 dB | 46.3 dB | 44.3 dB | 41.8 dB | 38.8 dB | 26 dB | na dB | 100 ± 15 Ohm | |
| 25 MHz | 9.5 dB/100m | 53.3 dB | 51.3 dB | 43.8 dB | 41.8 dB | 39.8 dB | 36.8 dB | 25.3 dB | na dB | 100 ± 15 Ohm | |
| 31.25 MHz | 10.7 dB/100m | 51.9 dB | 49.9 dB | 41.2 dB | 39.2 dB | 37.9 dB | 34.9 dB | 24.6 dB | na dB | 100 ± 15 Ohm | |
| 62.5 MHz | 15.4 dB/100m | 47.4 dB | 45.4 dB | 32 dB | 30 dB | 31.9 dB | 28.9 dB | 22.5 dB | na dB | 100 ± 15 Ohm | |
| 100 MHz | 19.8 dB/100m | 44.3 dB | 42.3 dB | 24.5 dB | 22.5 dB | 27.8 dB | 24.8 dB | 21.1 dB | na dB | 100 ± 15 Ohm | 100 ± 15 Ohm |
| 155 MHz | 25.2 dB/100m | 41.5 dB | 39.5 dB | 16.3 dB | 14.3 dB | 23.9 dB | 20.9 dB | 19.8 dB | na dB | 100 ± 22 Ohm | 100 ± 15 Ohm |
| 200 MHz | 29 dB/100m | 39.8 dB | 37.8 dB | 10.8 dB | 8.8 dB | 21.8 dB | 18.8 dB | 19 dB | na dB | 100 ± 22 Ohm | 100 ± 15 Ohm |
| 250 MHz | 32.8 dB/100m | 38.3 dB | 36.3 dB | 5.5 dB | 3.5 dB | 19.8 dB | 16.8 dB | 18.3 dB | na dB | 100 ± 32 Ohm | 100 ± 15 Ohm |

Voltage

| UL Description | UL Voltage Rating |
|---------------------------|-------------------|
| | 300V RMS |
| Appliance Wiring Material | 600 V RMS |

Applicable Standards & Environmental Programs

| | |
|------------------------------------|-------------------------------|
| CEC/C(UL) Specification: | CMG |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU Directive 2012/19/EU (WEEE): | Yes |
| EU Directive 2015/863/EU: | Yes |
| EU Directive Compliance: | EU Directive 2003/11/EC (BFR) |
| EU CE Mark: | Yes |

| | |
|---------------------------------------|---|
| EU RoHS Compliance Date (yyyy-mm-dd): | 2004-01-04 |
| CPR Euroclass: | Eca |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |
| Telecommunications Standards: | Category 6 - TIA 568.C.2 |
| Other Specification: | NEMA WC-63.1 Category 6, |
| Patent: | http://www.belden.com/p |

Standards

| | |
|-------------------------|-------------------------------------|
| ISO/IEC Compliance: | ISO/IEC 11801 ed 2.1 (2008) Class E |
| ANSI/TIA Category: | Category 6 |
| NEC/(UL) Specification: | CMR, CMX-Outdoor |
| UL AWM Style: | UL Style 21047 |

Flame Test

| | |
|---------------------|--------------|
| CSA Flammability: | FT4 |
| C(UL) Flammability: | FT4 |
| IEEE Flammability: | 1202 |
| UL Flammability: | UL1666 Riser |

Safety

| | |
|--------------------|-----------|
| UL Voltage Rating: | 300 V RMS |
|--------------------|-----------|

Suitability

| | |
|------------------------------------|-----|
| Suitability - Aerial: | Yes |
| Suitability - Burial: | No |
| Suitability - Indoor: | Yes |
| Suitability - Oil Resistance: | Yes |
| Suitability - Outdoor: | Yes |
| Suitability - Sunlight Resistance: | Yes |

Mechanical Characteristics

| | |
|----------------------------------|----------------|
| Storage Temp Range: | -40°C To +80°C |
| Installation Temp Range: | -25°C To +75°C |
| Operating Temp Range: | -40°C To +75°C |
| Bulk Cable Weight: | 44(lbs/1000ft) |
| Max Recommended Pulling Tension: | 40(lbs) |
| Min Bend Radius/Minor Axis: | 4(in) |

Temperature Range

| | |
|-----------------|------|
| UL Temp Rating: | 75°C |
|-----------------|------|

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

History

Variants

| Item # | Color |
|---------------|-------|
| 7953A 0101000 | BLACK |
| 7953A 0105000 | BLACK |
| 7953A 0061000 | BLUE |
| 7953A 0081000 | GRAY |

| | |
|---------------|------|
| 7953A 0021000 | RED |
| 7953A 1NH1000 | TEAL |

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.