

Part Number: 7953A

DataTuff® Cat 6, (4 pr) 23 AWG Solid BC, PP/PVC/PVC, EtherNet/IP, Foil Shld, CMR, CMX, 600 V AWM



Product Description

Four Cat 6 23 AWG Bonded-Pairs solid bare copper conductors, polypropylene insulation, FRPE spline center member, inner PVC jacket, overall Beldfoil® Shield (100% coverage), industrial grade oil- and UV-resistant PVC outer jacket.

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155 ATM, 622 ATM, 250MHz Category 6
------------------------	--

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Pairs
	23	Solid	BC - Bare Copper	4
No Ground				

Conductor Count:	8
Total Number of Pairs:	4
AWG Size:	23

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.043 in	0.01 in

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Inner Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
Industrial Grade PVC - Polyvinyl Chloride	0.258 in	0.02 in	Yes

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
Industrial Grade PVC - Polyvinyl Chloride	0.335 in	0.03 in	No

Construction and Dimensions

Cabling

Filler
X-Spline Center Member

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
8.2 Ohm/1000ft	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/ft	15 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
537 ns/100m	45 ns/100m	72 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)
1 MHz	2 dB/100m	74.3 dB	72.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	21 dB	100 ± 15 Ohm
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	61.5 dB	59.5 dB	55.8 dB	52.7 dB	24 dB	100 ± 15 Ohm
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	55.4 dB	53.4 dB	49.7 dB	46.7 dB	25.5 dB	100 ± 15 Ohm
10 MHz	6 dB/100m	59.3 dB	57.3 dB	53.3 dB	51.3 dB	47.8 dB	44.8 dB	26 dB	100 ± 15 Ohm
16 MHz	7.6 dB/100m	56.2 dB	54.3 dB	48.7 dB	46.7 dB	43.7 dB	40.7 dB	26 dB	100 ± 15 Ohm
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	46.3 dB	44.3 dB	41.8 dB	38.8 dB	26 dB	100 ± 15 Ohm
25 MHz	9.5 dB/100m	53.3 dB	51.3 dB	43.8 dB	41.8 dB	39.8 dB	36.8 dB	25.3 dB	100 ± 15 Ohm
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	41.2 dB	39.2 dB	37.9 dB	34.9 dB	24.6 dB	100 ± 15 Ohm
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	32 dB	30 dB	31.9 dB	28.9 dB	22.5 dB	100 ± 15 Ohm
100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	24.5 dB	22.5 dB	27.8 dB	24.8 dB	21.1 dB	100 ± 15 Ohm
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	16.3 dB	14.3 dB	23.9 dB	20.9 dB	19.8 dB	100 ± 22 Ohm
200 MHz	29 dB/100m	39.8 dB	37.8 dB	10.8 dB	8.8 dB	21.8 dB	18.8 dB	19 dB	100 ± 22 Ohm
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	5.5 dB	3.5 dB	19.8 dB	16.8 dB	18.3 dB	100 ± 32 Ohm

Voltage

UL Description	UL Voltage Rating
	300V RMS
Appliance Wiring Material	600 V RMS

Temperature Range

Installation Temp Range:	-25°C To +75°C
UL Temp Rating:	75°C
Storage Temp Range:	-40°C To +80°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	44 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius/Minor Axis:	4 in

Standards

NEC/(UL) Specification:	CMR, CMX-Outdoor
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 21047
ISO/IEC Compliance:	ISO/IEC 11801 ed 2.1 (2008) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
Telecommunications Standards:	Category 6 - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 6,

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes

EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-04
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes
Suitability - Burial:	No
Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser
CSA Flammability:	FT4
IEEE Flammability:	1202

Part Number

Plenum (Y/N):	No
---------------	----

Variants

Item #	Color	Footnote
7953A 0101000	BLACK	C
7953A 0105000	BLACK	C
7953A 0061000	BLUE	C
7953A 0081000	GRAY	C
7953A 0021000	RED	C
7953A 1NH1000	TEAL	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	http://www.belden.com/p

Product Notes

Notes:	US Patent #'s 5, 606, 151; 5, 734, 126. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. Not intended for 600 V electrical power delivery. T568A Plug Compatible Part Number: R301603 T568B Plug Compatible Part Number: R301604 T568A Plug Compatible Part Number: R301603 T568B Plug Compatible Part Number: R301604
--------	--

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.