



Product: [7962A](#)

DataTuff® Cat 5e, Quad (2 Pr) #22 Str TC, PO Ins, OS+TC Brd, TPE Jkt, CM CMX-Outdoor

[Request Sample](#)

Product Description

Industrial Ethernet Cat 5e, Quad (2 Pair) 22AWG (19x34) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, TPE Outer Jacket, CM CMX-Outdoor

Technical Specifications

Product Overview

Suitable Applications:	PROFINET, outdoor, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
------------------------	---

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Elements
Quad(s)	22 AWG	19x34	TC - Tinned Copper	1

Insulation

Material	Color Code
PO - Polyolefin	White, Blue, Yellow, Orange

Inner Jacket

Material	Nom. Diameter
PE - Polyethylene	0.169 in (4.29 mm)

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	85%

Outer Jacket

Material	Nom. Diameter	Ripcord
TPE - Thermoplastic Elastomer	0.276 in (7.01 mm)	No

Overall Cable Diameter (Nominal):	0.276 in (7.01 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
57 Ohm/km (17 Ohm/1000ft)	150 pF/ft

Delay

Max. Delay	Nom. Velocity of Prop.
552 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.1 dB/100m	65.3	62.3	63.2	63.8	60.8	23	100 ± 20.2	105 ± 10

4	4.0 dB/100m	56.3	53.3	56.3	51.7	48.7	23	100 ± 14.2	100 ±10
8	5.6 dB/100m	51.8	48.8	46.2	45.7	42.7	23	100 ± 11.3	100 ±10
10	6.3 dB/100m	50.3	47.3	43.9	43.8	40.8	25	100 ± 11.3	100 ±10
16	8.0 dB/100m	47.3	44.3	35.2	39.7	36.7	25	100 ± 11.3	100 ±10
20	9.0 dB/100m	45.8	42.8	36.5	37.7	34.7	25	100 ± 11.3	100 ±10
25	10.1 dB/100m	44.3	41.3	34.2	35.8	32.8	25.5	100 ± 11.3	100 ±10
31.25	11.4 dB/100m	42.9	39.9	31.3	33.9	30.9	23.6	100 ± 13.2	100 ±10
62.5	16.5 dB/100m	38.4	35.4	21.6	27.8	24.8	21.5	100 ± 16.9	100 ±10
100	21.3 dB/100m	35.3	32.3	17.1	23.8	20.8	20.1	100 ± 20.0	100 ±10

Voltage

UL Voltage Rating
300 V (CM, CMX-Outdoor), 600 V (AWM 20626)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
75°C	-40°C To +80°C	-20°C To +60°C	-40°C To +80°C

Bend Radius

Stationary Min.	
2.560 in (65.02 mm)	
Max. Pull Tension:	55 lbs (25 kg)
Bulk Cable Weight:	45 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL 1685 (UL Loading), FT4, IEEE 1202 Vertical Tray Flame Test
NEC / UL Compliance:	Article 800, CM, CMX-Outdoor, ITC, PLTC
AWM Compliance:	AWM 20626
CEC / C(UL) Compliance:	CMX-Outdoor
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-6
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Operating Temperature subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. Limits below 4 MHz are for information only.
--------	--

History

Update and Revision:	Revision Number: 0.426 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN
7962A+0085	Green	Reel	85 m	8719605196156
7962A.00305	Green	Reel	305 m	8719605016812
7962A.00610	Green	Reel	610 m	8719605016829
7962A 1SW1000	Green, RAL 6018			612825367024
7962A 1SW2000	Green, RAL 6018			612825367031

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.