



Product: [7987P](#) 



NanoSkew™ 4-24 AWG pairs, CMP

Product Description

NanoSkew™ 24 AWG twisted pairs solid bare copper conductors, FEP insulation, rip cord, Flamarrest® jacket.

Technical Specifications

Product Overview

Suitable Applications:	UTP Based Video Applications, Not for data transmission requiring TIA/EIA Category qualifications, RGB
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
FEP - Fluorinated Ethylene Propylene	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.201 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR
90 Ohm/km

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Typical Delay Skew

0.007 ns/100m

High Freq

Frequency [MHz]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	100 ± 15	100 ± 15
4 MHz	100 ± 15	100 ± 15
8 MHz	100 ± 15	100 ± 15
10 MHz	100 ± 15	100 ± 15
16 MHz	100 ± 15	100 ± 15
20 MHz	100 ± 15	100 ± 15
25 MHz	100 ± 15	100 ± 15
31.25 MHz	100 ± 15	100 ± 15
62.5 MHz	100 ± 15	100 ± 15
100 MHz	100 ± 15	100 ± 15

Voltage**UL Voltage Rating**

300 V RMS

Temperature Range

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	21 lbs/1000ft
Max. Pull Tension:	40 lbs
Min Bend Radius/Minor Axis:	0.2 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	7987R
--------------------	-------

Variants

Item #	Color	Putup Type	Length	UPC
7987P 1NDU1000	Maroon 1ND	UnReel	1,000 ft	612825192503

7987P 1NDU1640	Maroon 1ND	UnReel	1,640 ft	612825192510
----------------	------------	--------	----------	--------------

Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals.
--------	--

History

Update and Revision:	Revision Number: 0.287 Revision Date: 04-28-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.