


Part Number: 7987R

NanoSkew™ 4-24 AWG pairs, CMR



Product Description

NanoSkew™ 24 AWG twisted pairs solid bare copper conductors, non-plenum, polyolefin insulation, skew 2.2ns/100m nominal, rip cord, PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor - Riser
Suitable Applications:	Zero Skew, Low Skew, RJ45, UTP Based Video Applications, Not for data transmission requiring TIA/EIA Category qualifications, RGB

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	24 AWG

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Material	
Unshielded	

Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.195 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	
90 Ohm/km	

Impedance

Nominal Characteristic Impedance	
100 Ohm	

Delay

Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
70 %	0.007 ns/100m

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	18 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius/Minor Axis:	0.2 in

Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	7987P

Part Number

Variants

Item #	Color
7987R 059U1000	Maroon
7987R 059U1000	Maroon
7987R 059U1640	Maroon
7987R 059U1640	Maroon

Patent:	https://www.belden.com/resources/patents
---------	-------------------------------------------------------------------------------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.