


Part Number: 7988P

Low Skew, Category 5e, 4-24 AWG pairs, CMP



Product Description

Category 5e, 24 AWG bonded pairs solid bare copper conductors, plenum, FEP Teflon® insulation, skew 9.0ns/100m nominal, rip cord, Flamarrest® jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor - Plenum
Suitable Applications:	Category 5e, UTP Based Video Applications, and KVM

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	FEP - Fluorinated Ethylene Propylene
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Material	Unshielded
-----------------	------------

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.193 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
90 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	66
-----------------------------------	----

Delay

Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
72 %	0.027 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	65.3 dB	65.3 dB	60.3 dB	60.3 dB	63.8 dB	60.8 dB	20 dB	100 ± 15	100 ± 15
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	49.2 dB	49.2 dB	51.7 dB	48.7 dB	23 dB	100 ± 15	100 ± 15
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	43 dB	43 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 15	100 ± 15
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	40.8 dB	40.8 dB	43.8 dB	40.8 dB	25 dB	100 ± 15	100 ± 15
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	36 dB	36 dB	39.7 dB	36.7 dB	25 dB	100 ± 15	100 ± 15
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	33.5 dB	33.5 dB	37.7 dB	34.7 dB	25 dB	100 ± 15	100 ± 15
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	30.9 dB	30.9 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15	100 ± 15
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	28.2 dB	28.2 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15	100 ± 15
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	18.4 dB	18.4 dB	27.8 dB	24.8 dB	21.5 dB	100 ± 15	100 ± 15
100 MHz	22 dB/100m	35.3 dB	32.3 dB	10.3 dB	10.3 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 15	100 ± 15
155 MHz	28.1 dB/100m	32.5 dB	29.54 dB	2 dB	2 dB	19.9 dB	16.9 dB	15.8 dB	100 ± 25	100 ± 15
200 MHz	32.4 dB/100m	30.8 dB	27.8 dB	1 dB	1 dB	17.7 dB	14.7 dB	15 dB	100 ± 25	100 ± 15

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	21 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius/Minor Axis:	2 in

Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	ISO11801 Category 5
Telecommunications Standards:	ANSI/TIA/EIA-568-B.2 Category 5e
Other Specification:	NEMA WC-63.1 Category 5e, UL Verified to Category 5e

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N): Yes

Part Number

Non-Plenum Number: 7988R

Variants

Item #	Color	UPC	Length
7988P N3UU1000	Green, Mil	612825192541	1,000 ft
7988P N3UU1000	Green, Mil	612825192541	1,000 ft

Patent: <https://www.belden.com/resources/patents>

Product Notes

Notes: Jacket sequentially marked at 2 ft. intervals. Electricals are preliminary, final data is pending.

History

Update and Revision: Revision Number: 0.270 Revision Date: 08-22-2019

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.