



**Product:** [7989R](#) 



Low Skew, Category 6, 4-24 AWG pairs, CMR

**Product Description**

Category 6, 23 AWG bonded pairs solid bare copper conductors, non-plenum, polyolefin insulation, skew 10.0ns/100m nominal, rip cord, PVC jacket.

**Technical Specifications**

**Product Overview**

Suitable Applications:	Category 6, UTP Based Video Applications, and KVM
------------------------	---

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

**Insulation**

Material
PO - Polyolefin

Bonded-Pair:	N/A
--------------	-----

**Color Chart**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

**Outer Shield Material**

Material
No Shield

**Outer Jacket Material**

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.365 in	Yes

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR	Max. DCR Unbalance
90 Ohm/km	3 %

**Capacitance**

Max. Capacitance Unbalance	Nom. Mutual Capacitance
49.2	15 pF/ft

**Delay**

**Typical Delay Skew**

0.03 ns/100m

**High Freq**

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)
1 MHz	2 dB/100m	74.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	20 dB	100 ± 15
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	59.5 dB	55.7 dB	52.7 dB	23 dB	100 ± 15
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15
10 MHz	6 dB/100m	59.3 dB	57.3 dB	51.3 dB	47.8 dB	44.8 dB	25 dB	100 ± 15
16 MHz	7.6 dB/100m	56.3 dB	54.3 dB	46.7 dB	43.7 dB	40.7 dB	25 dB	100 ± 15
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	44.3 dB	41.7 dB	38.7 dB	25 dB	100 ± 15
25 MHz	9.5 dB/100m	53.4 dB	51.4 dB	41.8 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	39.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	30 dB	31.8 dB	28.8 dB	21.5 dB	100 ± 15
100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	22.5 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	14.3 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 22
200 MHz	29 dB/100m	39.8 dB	37.8 dB	8.8 dB	21.8 dB	18.7 dB	18 dB	100 ± 22
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	3.5 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 32

**Voltage****UL Voltage Rating**

300 V RMS

**Temperature Range**

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

**Mechanical Characteristics**

Bulk Cable Weight:	29 lbs/1000ft
Max. Pull Tension:	50 lbs
Min Bend Radius/Minor Axis:	1.75 in

**Standards**

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

**Applicable Environmental and Other Programs**

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
MII Order #39 (China RoHS):	Yes

**Flammability, LSOH, Toxicity Testing**

UL Flammability:	UL1666 Vertical Shaft
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

**Plenum/Non-Plenum**

Plenum (Y/N):	No
Plenum Number:	7989P

**Part Number****Variants**

Item #	Color	Putup Type	Length	UPC
--------	-------	------------	--------	-----

7989R 0131000	Blue, Dark	Reel	1,000 ft	612825192602
---------------	------------	------	----------	--------------

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	US Patent #'s 5, 606, 151; 5, 734, 126.
--------	---

## History

Update and Revision:	Revision Number: 0.244 Revision Date: 04-28-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.