



Product: [7999AP](#)

Broadband Coax, Series 11, 14 AWG Solid BCCS, Quad Shield, PVDF Jkt, CMP

Product Description

Broadband Coax, Series 11, 14 AWG Solid Bare Copper Covered Steel Conductor, FEP Insulation, Foil + 60% Aluminum Braid + Foil + 40% Aluminum Braid Shield, PVDF Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Direct Broadcast Satellite (DBS), Over-The-Air (OTA) antennas
------------------------	--

Construction Details

RG Type:	11
Series Type:	11

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	14 AWG	Solid	0.064 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in (6.96 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Aluminum		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Aluminum		40%

Outer Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.372 in (9.45 mm)

Overall Cable Diameter (Nominal):	0.372 in (9.45 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Structural Return Loss
5 - 1000 MHz	20 dB
1000 - 2250 MHz	15 dB
2250 - 3000 MHz	10 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.2 dB/100ft
10 MHz	0.5 dB/100ft

50 MHz	0.9 dB/100ft
100 MHz	1.3 dB/100ft
200 MHz	1.9 dB/100ft
400 MHz	2.8 dB/100ft
700 MHz	3.9 dB/100ft
750 MHz	4.3 dB/100ft
900 MHz	4.7 dB/100ft
1000 MHz	5.0 dB/100ft
1450 MHz	6.7 dB/100ft
1800 MHz	7.7 dB/100ft
2250 MHz	8.5 dB/100ft
3000 MHz	9.9 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
11 Ohm/1000ft (36 Ohm/km)	3 Ohm/1000ft (9.8 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating	Voltage Rating
300 V RMS	300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-20°C To +150°C

Bend Radius

Stationary Min.	Installation Min.
3.75 in (95.3 mm)	3.75 in (95.3 mm)

Max. Pull Tension: 260 lbs (120 kg)

Bulk Cable Weight: 63 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, FT6
NEC / UL Compliance:	Article 800, CATVP, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	7999A

Product Notes

Notes:	PF_7999AP 1)# Elements@Conductor1:-In Stibo it was Blank and now changed to 1. 2)Size@Conductor1 :-In Stibo it was 14 now changed to 14AWG. 3)Color@Color Chart1 01 :- In stibo it was Blank now Changed to White. 4)Material@OuterShield1 1 - In stibo it is Tri-Laminate (Alum+Poly+Alum) But in BPCS (Heat fusible+ Alum+ Poly+Alum 5)Material@OuterShield1 3 - In stibo it is Tri-Laminate (Alum+Poly+Alum) But in BPCS (Alum+ Poly+Alum+microcapsulated mineral oil. 6)Cable Diameter (Nominal)- In Stibo it was Blank Now Changed to 0.372 in. 7)Bulk Cable Weight - In stibo it was 62 lbs/1000 ft Now changed to 63 lbs/1000 ft.
--------	--

History

Update and Revision:	Revision Number: 0.475 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7999AP 0101000	Black	Reel	1,000 ft	612825195917	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.