



Part Number: 8213

Analog Video, RG11, #14 Solid BC, 95% BC Braid, PE Jacket

Product Description

14 AWG solid .064" bare copper conductor, gas-injected foam HDPE insulation, bare copper braid shield (95% coverage), polyethylene jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor/Outdoor
----------------------	----------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	BC - Bare Copper	0.064 in	1

Conductor Count:	1
AWG Size:	14

Insulation

Material	Nominal Diameter
Gas-injected FHDPE - Foam High Density Polyethylene	0.285 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	BC - Bare Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
PE - Polyethylene	0.405 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
2.6 Ohm/1000ft	2.6 Ohm/1000ft	1.1 Ohm/1000ft	1.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.1 pF/ft

Inductance

Nominal Inductance
0.097 μ H/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
5-450 MHz	23 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss	Nom. Structural Return Loss (SRL)
1 MHz	0.2 dB/100ft	23 dB
450 MHz	0.4 dB/100ft	
5 MHz	0.9 dB/100ft	
100 MHz	1.3 dB/100ft	
200 MHz	1.9 dB/100ft	
400 MHz	2.9 dB/100ft	
700 MHz	4.1 dB/100ft	
900 MHz	4.8 dB/100ft	
1000 MHz	5.2 dB/100ft	

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.21 ns/ft	84 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
400 MHz	4.4 dB/100ft
10 MHz	
50 MHz	
100 MHz	
200 MHz	
400 MHz	
700 MHz	
900 MHz	
1000 MHz	

Voltage

Non-UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-55°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	78 lbs/1000ft
Max Recommended Pulling Tension:	171 lbs
Min Bend Radius/Minor Axis:	4 in

Standards

RG Type:	RG-11/U Type
Series Type:	Series 11

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	Yes

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Part Number

Plenum (Y/N):	No
---------------	----

Variants

Item #	Color
8213.00305	BLACK

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.