



Product: [80112](#) 

ECOFLEX PUR, 9C #24, Str, MPPE, 600 V, AWM/STYLE 11231 105C, AWM/STYLE 21959 90C, 60C OIL, SUN RES, CSA C(RU) AWM I/II A/B, CSA FT2

Product Description

ECOFLEX PUR, 9 Conductor 24 AWG (19/36) TC - Tinned Copper, MPPE Insulation, Overall Tinned Copper Shield, Slate Polyurethane, Zero Halogen (ZH) Outer Jacket, AWM/STYLE 11231 105C, AWM/STYLE 21959 90C, 60C OIL, SUN RES, CSA C(RU) AWM I/II A/B, CSA FT2 C(RU) AWM I/II A/B, FT2 UL FT2; CSA FT2; EN 60754-1 Acid Gas Generation; EN 60754-2 Acid Gas Generation; EN 60332-1 Flame Behavior; EN 60332-2 Flame Behavior

Technical Specifications

Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	9	24 AWG	19x36	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	mPPE - Modified Polyphenylene Ether	0.010 in (0.25 mm)	0.045 in (1.1 mm)	Green/Yellow, Black#1, Black#2, Black#3, Black#4, Black#5, Black#6, Black#7, Black#8

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	85%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PUR - Polyurethane (Halogen Free)	0.032 in (0.81 mm)	0.279 in (7.09 mm)

Overall Cable Diameter (Nominal):	0.279 in (7.09 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance
Conductor(s)	27 pF/ft (89 pF/m)	49 pF/ft (160 pF/m)	0.19 μH/ft (0.62 μH/m)

Nom Outer Shield DCR:	42 Ohm/1000ft (140 Ohm/km)
-----------------------	----------------------------

Voltage

UL Voltage Rating	Voltage Rating
600 V (AWM 11231, AWM 21959)	600 V (CSA AWM)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
105°C	-50°C To +90°C	-40°C To +80°C

Bend Radius

Stationary Min.

2.8 in (71 mm)

Max. Pull Tension: 106 lbs (48.1 kg)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1685 FT2 Loading, FT2, IEC 60332-1-2, IEC 60332-2-2
AWM Compliance:	AWM 21959, AWM I/II A/B
ISO/IEC Compliance:	IEC 60754-1, IEC 60754-2, IEC 60228 Class 6
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alpha Wire -* P/N 80112 9C 24 AWG RU AWM STYLE 21959 90C 600V SUN RES 60C OIL OR CRU AWM I/II A/B 90C 600V FT2 --- IEC EN 60332-1/2 CE ROHS (SEQ FOOTAGE)
--------	-----------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.17 Revision Date: 06-30-2026
----------------------	-------------------------------------------------

Part Numbers**Variants**

Item #	Color
80112 SL005	Green/Yellow
80112 SL199	Green/Yellow

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.