



Part Number: 8216
50 Ohm, RG174, 26 AWG

Product Description

RG-174/U type, 26 AWG stranded (7x34) .019" bare copper-covered steel conductor, polyethylene insulation, tinned copper braid shield (90% coverage), PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Outdoor - Aerial
----------------------	------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
26	7x34	BCCS - Bare Copper Covered Steel	0.019 in	1

Conductor Count:	1
Conductor Size:	26 AWG

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.06 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	90 %

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.11 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
97 Ohm/1000ft	10.7 Ohm/1000ft	10.7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
30.8 pF/ft

Inductance

Nominal Inductance
0.077 μ H/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1.9 dB/100ft
10 MHz	3.3 dB/100ft
50 MHz	5.8 dB/100ft
100 MHz	8.4 dB/100ft
200 MHz	12.5 dB/100ft
400 MHz	19 dB/100ft
700 MHz	27 dB/100ft
900 MHz	31 dB/100ft
1000 MHz	34 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

Power Rating

Frequency [MHz]	Max. Power Rating [W]
1 MHz	976 W
10 MHz	354 W
50 MHz	197 W
100 MHz	161 W
200 MHz	136 W
400 MHz	120 W
700 MHz	112 W
900 MHz	109 W
1,000 MHz	108 W

Voltage

Non-UL Voltage Rating	UL Voltage Rating
1100 V RMS (Mil-Spec)	30 V RMS (UL AWM Style 1354)

Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	8 lbs/1000ft
Max Recommended Pulling Tension:	21 lbs
Min Bend Radius/Minor Axis:	1 in

Standards

UL AWM Style:	UL Style 1354
CPR Euroclass:	Eca
RG Type:	174/U Type

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Flammability, LSOH, Toxicity Testing

UL voltage rating:	30 V RMS (UL AWM Style 1354)
--------------------	------------------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
8216 010100	Black	
8216 0101000	Black	G N
8216 010500	Black	

Footnote:	G - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 100'.
-----------	---

Footnote:	N - FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.
-----------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.