

**Part Number: 8219**

54 Ohm, RG58, 20 AWG, CM



## Product Description

RG-58A/U type, 20 AWG stranded (19x32) .037" tinned copper conductor, foam polyethylene insulation, tinned copper braid shield (95% coverage), PVC jacket.

## Technical Specifications

### Product Overview

Environmental Space:	Outdoor - Aerial
----------------------	------------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	19x32	TC - Tinned Copper	0.037 in	1

Conductor Count:	1
AWG Size:	20

#### Insulation

Material	Nominal Diameter
FPE - Foamed Polyethylene	0.116 in

#### Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	95 %

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.193 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
8.8 Ohm/1000ft	4.1 Ohm/1000ft	4.1 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
26.5 pF/ft

#### Inductance

Nominal Inductance
0.065 µH/ft

#### Impedance

Nominal Characteristic Impedance
53.5 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.4 dB/100ft

10 MHz	1.3 dB/100ft
50 MHz	3.1 dB/100ft
100 MHz	4.5 dB/100ft
200 MHz	6.6 dB/100ft
400 MHz	10 dB/100ft
700 MHz	14.2 dB/100ft
900 MHz	16.6 dB/100ft
1000 MHz	18.1 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.39 ns/ft	73 %

#### Voltage

UL Voltage Rating
30V RMS (UL AWM Style 1354), 300V RMS (UL CM)
300V RMS (CM)

#### Temperature Range

UL Temp Rating:	80°C
Operating Temp Range:	-40°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	26 lbs/1000ft
Max Recommended Pulling Tension:	50 lbs
Min Bend Radius/Minor Axis:	2 in

#### Standards

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
UL AWM Style:	UL Style 1354
CPR Euroclass:	Fca
PMSHA Specification:	SC-182/5
RG Type:	RG-58A/U Type

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
------------------	-------------------

#### Part Number

Plenum (Y/N):	No
---------------	----

#### Variants

Item #	Color	Footnote
8219 0101000	BLACK	C
8219 010500	BLACK	C
8219 010U1000	BLACK	
8219 010U500	BLACK	
8219 0091000	WHITE	C
8219 009U500	WHITE	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.