



Product: [8233A](#) 

Triax, RG11, 14 AWG Solid BC, Double BC Braids, PVC Jkt, CMR

Product Description

Triax, RG11, 14 AWG Solid Bare Copper Conductor, PE Insulation, 95% Bare Copper Braid Shield, PVC Insulation, 80% Bare Copper Braid Shield, PVC Jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Analog Video; Interconnect camera to CCU (camera control unit)
------------------------	--

Construction Details

RG Type:	11
----------	----

Conductor

AWG	Stranding	Nom. Diameter	Material
14	Solid	0.064 in	BC - Bare Copper

Insulation

Material	Nom. Diameter
PE - Polyethylene (Foam)	0.285 in

Inner Shield Material

Layer	Inner Shield Type	Material	Coverage
1	Braid	Bare Copper (BC)	95%

Inner Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.365 in

Outer Shield Material

Layer	Outer Shield Type	Material	Coverage
1	Braid	Bare Copper (BC)	80%

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.475 in

Electrical Characteristics

Return Loss (RL)

Frequency [MHz]	Min. Return Loss [dB]
5 - 850 MHz	21 dB
850 - 4500 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.14 dB/100ft
3.6 MHz	0.30 dB/100ft

10 MHz	0.40 dB/100ft
71.5 MHz	1.10 dB/100ft
135 MHz	1.60 dB/100ft
270 MHz	2.30 dB/100ft
360 MHz	2.60 dB/100ft
540 MHz	3.30 dB/100ft
720 MHz	3.80 dB/100ft
750 MHz	4.00 dB/100ft
1000 MHz	4.60 dB/100ft
1500 MHz	5.90 dB/100ft
2250 MHz	7.40 dB/100ft
3000 MHz	9.00 dB/100ft
4500 MHz	12.50 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
2.6 Ohm/1000ft	1.7 Ohm/1000ft	1.5 Ohm/1000ft	16.1 pF/ft	75 Ohm	84%

Voltage

UL Voltage Rating
300 V (CMR, CMG)

Mechanical Characteristics

Temperature

UL Rating	Operating
60°C	-30°C to +75°C

Bend Radius

Installation Min.
5.0 in

Bulk Cable Weight:	125 lbs/1000ft
Max. Pull Tension:	194 lbs

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1666 Vertical Shaft
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	8233P

History

Update and Revision:	Revision Number: 0.322 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.