



Product: [8233WB](#)

Video Triax, RG11, #14 Solid BC, CPE Jacket, Waterblocked, CM

Product Description

14 AWG solid .064" bare copper conductor, gas-injected foam HDLPE insulation, bare copper braids (95% & 80% coverage), flooded, CPE jacket.

Technical Specifications

Product Overview

Suitable Applications:	Indoor/Outdoor, Aerial - when supported by messenger wire
------------------------	---

Construction Details

RG Type:	11
Series Type:	11

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	14 AWG	Solid	0.064 in	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.285 in (7.24 mm)	White

Table Notes:	Gas Injected
--------------	--------------

Inner Shield

Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Inner Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.371 in (9.42 mm)

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	80%

Table Notes:	CoreGuard®
--------------	------------

Outer Jacket

Material	Nom. Diameter
CPE - Chlorinated Polyethylene	0.475 in (12.1 mm)

Overall Cable Diameter (Nominal):	0.475 in (12.1 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 - 850 MHz	21 dB
850 - 4500 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.14 dB/100ft
3.6 MHz	0.3 dB/100ft
10 MHz	0.4 dB/100ft
71.5 MHz	1.1 dB/100ft
135 MHz	1.6 dB/100ft
270 MHz	2.3 dB/100ft
360 MHz	2.6 dB/100ft
540 MHz	3.3 dB/100ft
720 MHz	3.8 dB/100ft
750 MHz	4 dB/100ft
1000 MHz	4.6 dB/100ft
1500 MHz	5.9 dB/100ft
2250 MHz	7.4 dB/100ft
3000 MHz	9 dB/100ft
4500 MHz	12.5 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
2.6 Ohm/1000ft (8.5 Ohm/km)	1.7 Ohm/1000ft (5.6 Ohm/km)	1.5 Ohm/1000ft (4.9 Ohm/km)	16.1 pF/ft (52.8 pF/m)	75 Ohm	84%

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
75°C	-30°C To +75°C	-20°C To +75°C	-30°C To +90 °C

Bend Radius

Stationary Min.	Installation Min.
4.75 in (121 mm)	4.75 in (121 mm)

Max. Pull Tension:	240 lbs (110 kg)
Bulk Cable Weight:	131 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, UV Resistance, Aerial - When supported by messenger wire
Flammability / Reaction to Fire:	UL1685 Vertical Tray, FT1
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Flooding grease between outer jacket and outer braid. Print legend includes sequential footage marks.
--------	---

History

Update and Revision:	Revision Number: 0.494 Revision Date: 09-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
8233WB 0101000	Black	Reel	1,000 ft	612825440048
8233WB 0102000	Black	Reel	2,000 ft	612825441076
8233WB 0103000	Black	Reel	3,000 ft	612825441168
8233WB 0104000	Black	Reel	4,000 ft	612825196686

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.