

Part Number: 8237

50 Ohm, RG8, 13 AWG, CMH



Product Description

RG-8/U type, 13 AWG stranded (7x21) .085" bare copper conductor, polyethylene insulation, bare copper braid shield (95% coverage), PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Outdoor - Aerial
----------------------	------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
13	7x21	BC - Bare Copper	0.085 in	1

Conductor Count:	1
Conductor Size:	13 AWG

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.285 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	BC - Bare Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.403 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
1.9 Ohm/1000ft	1.2 Ohm/1000ft	1.2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
28.5 pF/ft

Shielding:	Braid(s)
------------	----------

Inductance

Nominal Inductance
0.079 μ H/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.2 dB/100ft

10 MHz	0.6 dB/100ft
50 MHz	1.3 dB/100ft
100 MHz	1.9 dB/100ft
200 MHz	2.8 dB/100ft
400 MHz	4.2 dB/100ft
700 MHz	5.9 dB/100ft
900 MHz	6.9 dB/100ft
1000 MHz	7.4 dB/100ft
4000 MHz	23.2 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
50 MHz	1,200 W	1,200 W
100 MHz	800 W	800 W
400 MHz	320 W	320 W
1,000 MHz	180 W	180 W

Voltage

Non-UL Voltage Rating
3700 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	102 lbs/1000ft
Max Recommended Pulling Tension:	190 lbs
Min Bend Radius/Minor Axis:	4.25 in

Standards

NEC/(UL) Specification:	CMH
CEC/C(UL) Specification:	CMH
CPR Euroclass:	Eca
RG Type:	8/U Type
RG / Series Type:	8/U Type

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Plenum/Non-Plenum

Plenum (Y/N): No

Part Number

Variants

Item #	Color	Footnote
8237 010100	Black	C
8237 0101000	Black	C
8237 010500	Black	C

Footnote: C - CRATE REEL PUT-UP.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.