



Product: [82489](#)

Electronic, 4 C #18 Str TC, FEP Ins, PVC Jkt, CMP

Request Sample

### Product Description

Electronic Cable, 4 Conductor 18AWG (19x30) Tinned Copper, FEP Insulation, PVC Outer Jacket, CMP

### Technical Specifications

#### Product Overview

Suitable Applications:	indoor plenum applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	18 AWG	19x30	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	FEP - Fluorinated Ethylene Propylene	0.007 in (0.18 mm)	0.057 in (1.4 mm)	Black, Red, White, Green

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.177 in (4.50 mm)

Overall Cable Diameter (Nominal): 0.177 in (4.50 mm)

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	6.92 Ohm/1000ft	21 pF/ft (69 pF/m)	5 Amps per Conductor at 25°C

##### Voltage

UL Voltage Rating
300 V (CMP), 150 V (CL3P)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
75°C	0°C to +75°C

##### Bend Radius

Stationary Min.	Installation Min.
1.77 in (45.0 mm)	1.77 in (45.0 mm)

Max. Pull Tension:	98.8 lbs (44.8 kg)
Bulk Cable Weight:	29 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum)
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	8489

## History

Update and Revision:	Revision Number: 0.518 Revision Date: 02-03-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
82489 8771000	Natural	Reel	1,000 ft	612825197140	C
82489 877U1000	Natural	UnReel	1,000 ft	612825197133	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.