




REPRESENTATIVE IMAGE

Product: [8102NH](#) 

RS232/422 Low Cap, #24-2pr, FPO, O/A Foil+Braid, LSZH Jkt, Dca, 100Ω

Product Description

2-Pair, 24 AWG stranded (7x32) TC conductors, Datalene® insulation, twisted pairs, overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), 24 AWG stranded TC drain wire, LSZH jacket, Flame resistance IEC 60332-3-24 cat.C

Technical Specifications

Product Overview

Suitable Applications:	RS-232 extended distance applications; rs-422 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	2

Conductor Count:	4
------------------	---

Insulation

Material	Material Trade Name	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene (Foam)	Datalene®	1.24 mm	0.06 mm

Color Chart

Number	Color
Pair 1	White & Blue; Blue & White
Pair 2	White & Orange; Orange & White

Outer Shield

Type	Layer	Material	Material Trade Name	Thickness of Foil	Drainwire Material	Drainwire AWG	Min. Coverage [%]
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	9 / 12 µm	TC - Tinned Copper	24	
Braid	2	Tinned Copper (TC)					65%

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.9 mm	0.8 mm

Table Notes:	UV stabilised
--------------	---------------

Construction and Dimensions

Cabling

Description	Filler
2 fillers and 2 pairs twisted to cable core	Polypropylene

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
78.7 Ohm/km	13 Ohm/km

Capacitance

Max. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
45.9 pF/m	41 pF/m	72.2 pF/m	72.2 pF/m

Inductance

Nominal Pair Inductance
0.75 µH/m

Impedance

Nominal Characteristic Impedance
100 Ohm

Current

Element	Max. Recommended Current [A]
Conductor(s)	1.8 Amps per Conductor

Voltage

UL Voltage Rating	Voltage Rating [V]
AWM 2919: 30 V	300 V type CM V

Table Notes:	Type CM
--------------	---------

Temperature Range

Installation Temperature Range:	-15°C To +80°C
Storage Temperature Range:	-45°C To +80°C
Operating Temperature Range:	-15°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Max. Pull Tension:	120 N
Min Bend Radius (W/o Pulling Strength):	34.5 mm
Min. Bend Radius During Installation:	69 mm
Min Setting Radius:	69 mm

Standards

UL AWM Style Compliance:	AWM 2919 (30 V RMS)
CPR Euroclass:	Dca-s1,d1,a1
CENELEC Compliance:	EN 50290-2-20

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
----------------------	------------------------

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2, IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%
UL voltage rating:	30 V RMS (UL AWM Style 2919)

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
8102NH.00305	Gray	Reel	305 m	8719605017710

History

Update and Revision:	Revision Number: 0.237 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.