




Product: [8110NH](#) 

RS232/422 Low Cap, #24-10pr, FPO, O/A Foil+Braid, LSZH Jkt, Dca, 100Ω

Product Description

10-Pair, 24 AWG stranded (7x32) TC conductors, Datalene® insulation, twisted pairs, overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), 24 AWG stranded TC drain wire, LSZH jacket, Flame resistance EC 60332-3C

Technical Specifications

Product Overview

Suitable Applications:	Instrumentation and computer cable; For data transmission applications
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	10

Conductor Count:	20
------------------	----

Insulation

Material	Material Trade Name	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene (Foam)	Datalene®	1.24 mm	0.06 mm

Color Chart

Number	Color
Pair 1	White/Blue & Blue/White
Pair 2	White/Orange & Orange/White
Pair 3	White/Green & Green/White
Pair 4	White/Brown & Brown/White
Pair 5	White/Gray & Gray/White
Pair 6	Red/Blue & Blue/Red
Pair 7	Red/Orange & Orange/Red
Pair 8	Red/Green & Green/Red
Pair 9	Red/Brown & Brown/Red
Pair 10	Red/Gray & Gray/Red

Outer Shield

Type	Material	Material Trade Name	Thickness of Foil	Drainwire Material	Drainwire AWG	Min. Coverage [%]
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	9 / 12 µm	TC - Tinned Copper	AWG24/7	
Braid	Tinned Copper (TC)					65%

Outer Jacket

Material	Nominal Diameter	Min. Wall Thickness	Min. Average Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	10.29 mm	0.7 mm	0.813 mm

Construction and Dimensions

Cabling

Description	Filler
2 fillers and 10 pairs twisted to cable core	Polypropylene (2x)

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
78.7 Ohm/km	8.5 Ohm/km

Capacitance

Max. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
45.9 pF/m	41 pF/m	72.2 pF/m

Inductance

Nominal Pair Inductance
0.75 μ H/m

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
78%

Current

Element	Max. Recommended Current [A]
Conductor(s)	1.5 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Storage Temperature Range:	-45°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Max. Pull Tension:	400 N
Min. Bend Radius During Installation:	102.9 mm
Min Setting Radius:	51.45 mm

Standards

CENELEC Compliance:	EN 50290-2-27
---------------------	---------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 μ S/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
8110NH.00152	Chrome	Reel	152 m	8719605017895
8110NH.00305	Chrome	Reel	305 m	8719605017901
8110NH.00500	Chrome	Reel	500 m	8719605017918

History

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.